

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791753

Luminaire Tested: LER6D30D010-EC6DR7020359050-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR7020359050-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6320.5 lumens
Efficiency: N/A
Efficacy: 217.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791753

CATALOG NUMBER: LER6D30D010-EC6DR7020359050-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P791753

CATALOG NUMBER: LER6D30D010-EC6DR7020359050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	776407
5°	753335
10°	732345
15°	722737
20°	674883
25°	507010
30°	358405
35°	126954
40°	66751
45°	71109
50°	73635
55°	75015
60°	75477
65°	73889
70°	69737
75°	64589
80°	57321
85°	46510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 75504 cd/sqm



TEST NUMBER: P791753

CATALOG NUMBER: LER6D30D010-EC6DR7020359050-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	647.9	10.3
10°-20°	1777.1	28.1
20°-30°	1957.2	31.0
30°-40°	747.8	11.8
40°-50°	353.1	5.6
50°-60°	351.0	5.6
60°-70°	281.0	4.4
70°-80°	161.5	2.6
80°-90°	43.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4382.1	69.3
0°-40°	5129.9	81.2
0°-60°	5834.0	92.3
0°-90°	6320.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6320.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7106	
5°	6869	648
15°	6389	1777
25°	4206	1957
35°	952	748
45°	460	353
55°	394	351
65°	286	281
75°	153	162
85°	37	44
90°	0	



TEST NUMBER: P791753

CATALOG NUMBER: LER6D30D010-EC6DR7020359050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7106.0
2.5°	7031.8
5°	6868.6
7.5°	6732.5
10°	6600.9
12.5°	6489.5
15°	6389.4
17.5°	6147.5
20°	5804.3
22.5°	5064.0
25°	4205.6
27.5°	3661.0
30°	2840.8
32.5°	1835.0
35°	951.8
37.5°	514.2
40°	468.0
42.5°	464.7
45°	460.2
47.5°	450.0
50°	433.2
52.5°	414.0
55°	393.8
57.5°	371.3
60°	345.4
62.5°	316.1
65°	285.8
67.5°	252.0
70°	218.3
72.5°	184.5
75°	153.0
77.5°	120.4
80°	91.1
82.5°	64.1
85°	37.1
87.5°	14.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)