

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790594

Luminaire Tested: LER6D20D010-EC6DR7020359040-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P790594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR7020359040-6LBDDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2862.9 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790594

CATALOG NUMBER: LER6D20D010-EC6DR7020359040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P790594

CATALOG NUMBER: LER6D20D010-EC6DR7020359040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	351689
5°	341242
10°	331729
15°	327378
20°	305693
25°	229659
30°	162347
35°	57501
40°	30238
45°	32202
50°	33350
55°	33983
60°	34199
65°	33454
70°	31594
75°	29255
80°	25986
85°	21061

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 34204 cd/sqm



TEST NUMBER: P790594

CATALOG NUMBER: LER6D20D010-EC6DR7020359040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.5	10.3
10°-20°	804.9	28.1
20°-30°	886.5	31.0
30°-40°	338.7	11.8
40°-50°	159.9	5.6
50°-60°	159.0	5.6
60°-70°	127.3	4.4
70°-80°	73.2	2.6
80°-90°	19.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1984.9	69.3
0°-40°	2323.6	81.2
0°-60°	2642.6	92.3
0°-90°	2862.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2862.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3219	
5°	3111	293
15°	2894	805
25°	1905	887
35°	431	339
45°	208	160
55°	178	159
65°	129	127
75°	69	73
85°	17	20
90°	0	



TEST NUMBER: P790594

CATALOG NUMBER: LER6D20D010-EC6DR7020359040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3218.8
2.5°	3185.1
5°	3111.3
7.5°	3049.6
10°	2990.0
12.5°	2939.5
15°	2894.2
17.5°	2784.6
20°	2629.1
22.5°	2293.8
25°	1905.0
27.5°	1658.3
30°	1286.8
32.5°	831.2
35°	431.1
37.5°	232.9
40°	212.0
42.5°	210.5
45°	208.4
47.5°	203.8
50°	196.2
52.5°	187.5
55°	178.4
57.5°	168.2
60°	156.5
62.5°	143.2
65°	129.4
67.5°	114.2
70°	98.9
72.5°	83.6
75°	69.3
77.5°	54.5
80°	41.3
82.5°	29.0
85°	16.8
87.5°	6.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)