

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791834

Luminaire Tested: LER6D35BD010-EC6DR3020359035-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR3020359035-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3347.6 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791834

CATALOG NUMBER: LER6D35BD010-EC6DR3020359035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P791834

CATALOG NUMBER: LER6D35BD010-EC6DR3020359035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	823928	823928	823928
5°	800275	799338	800314
10°	693160	688271	692997
15°	452251	449826	447560
20°	224883	233322	224582
25°	113281	127740	110959
30°	45359	49416	39517
35°	21034	20146	16885
40°	9083	10082	8553
45°	6408	7956	6462
50°	2203	5787	2334
55°	1268	2402	1334
60°	888	1056	888
65°	580	580	580
70°	358	246	358
75°	0	148	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 7956 cd/sqm



TEST NUMBER: P791834

CATALOG NUMBER: LER6D35BD010-EC6DR3020359035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	946.5	28.3
10°-20°	1524.4	45.5
20°-30°	658.7	19.7
30°-40°	150.1	4.5
40°-50°	51.6	1.5
50°-60°	12.6	0.4
60°-70°	3.3	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3129.7	93.5
0°-40°	3279.8	98.0
0°-60°	3344.0	99.9
0°-90°	3347.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3347.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	10764	10764	10764	10764	10764	
5°	10415	10405	10403	10425	10416	947
15°	5707	5638	5676	5658	5648	1528
25°	1341	1392	1512	1357	1314	642
35°	225	230	216	214	181	153
45°	59	74	74	74	60	42
55°	10	10	18	11	10	9
65°	3	3	3	3	3	3
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P791834

CATALOG NUMBER: LER6D35BD010-EC6DR3020359035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	10764.2	10764.2	10764.2	10764.2	10764.2
2.5°	10692.8	10685.4	10689.7	10694.9	10697.1
5°	10415.4	10405.3	10403.2	10424.9	10415.9
7.5°	9855.7	9841.4	9819.8	9868.9	9914.9
10°	8918.2	8902.3	8855.3	8878.5	8916.1
12.5°	7534.1	7482.8	7481.8	7555.7	7545.7
15°	5707.1	5638.4	5676.5	5658.0	5647.9
17.5°	3837.9	3811.4	3862.2	3846.8	3780.8
20°	2760.8	2767.7	2864.4	2815.8	2757.1
22.5°	2014.6	2039.4	2154.1	2028.9	1982.9
25°	1341.3	1392.0	1512.5	1356.6	1313.8
27.5°	825.0	848.2	970.3	814.4	791.1
30°	513.2	501.5	559.1	479.9	447.1
32.5°	336.6	321.8	340.3	305.5	279.0
35°	225.1	229.9	215.6	214.0	180.7
37.5°	140.6	161.7	142.7	152.2	116.3
40°	90.9	117.3	100.9	111.5	85.6
42.5°	74.5	90.4	83.0	88.3	76.1
45°	59.2	73.5	73.5	73.5	59.7
47.5°	32.8	49.1	62.9	50.2	34.9
50°	18.5	24.8	48.6	25.9	19.6
52.5°	12.7	14.3	33.3	14.8	13.2
55°	9.5	10.0	18.0	10.6	10.0
57.5°	7.4	7.9	9.5	7.9	7.4
60°	5.8	5.8	6.9	6.3	5.8
62.5°	4.2	4.2	4.8	4.2	4.2
65°	3.2	3.2	3.2	3.2	3.2
67.5°	1.6	2.1	2.1	2.1	2.1
70°	1.6	1.1	1.1	1.1	1.6
72.5°	1.1	0.5	0.5	0.5	0.5
75°	0.0	0.0	0.5	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)