

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791934

Luminaire Tested: LER6D35BD010-EC6DR4020359035-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR4020359035-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4011.7 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791934
CATALOG NUMBER: LER6D35BD010-EC6DR4020359035-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P791934

CATALOG NUMBER: LER6D35BD010-EC6DR4020359035-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96											96																	
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92											92																	
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88											88																	
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84											84																	
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81											81																	
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77											77																	
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74											74																	
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72											72																	
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69											69																	
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67											67																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1020506
5°	1015554
10°	959918
15°	816046
20°	556203
25°	232070
30°	72973
35°	33919
40°	18756
45°	8607
50°	4181
55°	2286
60°	1202
65°	414
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8607 cd/sqm



TEST NUMBER: P791934

CATALOG NUMBER: LER6D35BD010-EC6DR4020359035-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	864.6	21.6
10°-20°	1936.9	48.3
20°-30°	969.6	24.2
30°-40°	177.7	4.4
40°-50°	49.1	1.2
50°-60°	11.5	0.3
60°-70°	2.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3771.1	94.0
0°-40°	3948.8	98.4
0°-60°	4009.4	99.9
0°-90°	4011.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4011.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9340	
5°	9259	865
15°	7214	1937
25°	1925	970
35°	254	178
45°	56	49
55°	12	12
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791934

CATALOG NUMBER: LER6D35BD010-EC6DR4020359035-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9340.1
2.5°	9326.5
5°	9259.4
7.5°	9045.5
10°	8652.1
12.5°	8038.8
15°	7214.3
17.5°	6142.2
20°	4783.6
22.5°	3261.2
25°	1925.0
27.5°	1017.6
30°	578.4
32.5°	373.8
35°	254.3
37.5°	181.7
40°	131.5
42.5°	90.0
45°	55.7
47.5°	35.5
50°	24.6
52.5°	17.5
55°	12.0
57.5°	7.6
60°	5.5
62.5°	3.3
65°	1.6
67.5°	1.1
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)