

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790698

Luminaire Tested: LER6D25D010-EC6DR2015309050-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR2015309050-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2968.8 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P790698
CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P790698

CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	95															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	96	94	93															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	94	92	91															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	92	90	89															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	90	88	87															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	88	86	85															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	86	84	83															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	84	82	81															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1846266
5°	1665671
10°	934867
15°	475208
20°	201199
25°	92876
30°	49166
35°	26490
40°	14163
45°	8375
50°	4861
55°	2572
60°	1639
65°	1163
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8375 cd/sqm



TEST NUMBER: P790698

CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1203.1	40.5
10°-20°	1184.7	39.9
20°-30°	387.0	13.0
30°-40°	131.8	4.4
40°-50°	44.3	1.5
50°-60°	13.3	0.4
60°-70°	4.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2774.8	93.5
0°-40°	2906.5	97.9
0°-60°	2964.2	99.8
0°-90°	2968.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2968.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16898	
5°	15187	###
15°	4201	1185
25°	770	387
35°	199	132
45°	54	44
55°	14	13
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790698

CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	16897.8
0.5°	16897.8
1°	16876.7
1.5°	16834.6
2°	16757.8
2.5°	16655.5
3°	16511.0
3.5°	16309.4
4°	16010.0
4.5°	15645.8
5°	15186.9
5.5°	14583.5
6°	13965.1
6.5°	13256.4
7°	12562.7
7.5°	11750.2
8°	11024.9
8.5°	10295.1
9°	9621.0
9.5°	9002.6
10°	8426.3
12.5°	6050.4
15°	4201.1
17.5°	2744.6
20°	1730.4
22.5°	1121.0
25°	770.4
27.5°	541.7
30°	389.7
32.5°	279.9
35°	198.6
37.5°	138.4
40°	99.3
42.5°	72.2
45°	54.2
47.5°	42.1
50°	28.6
52.5°	18.1
55°	13.5
57.5°	10.5
60°	7.5
62.5°	6.0
65°	4.5



TEST NUMBER: P790698

CATALOG NUMBER: LER6D25D010-EC6DR2015309050-6LBDP1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.0
70°		1.5

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)