

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790722

Luminaire Tested: LER6D25D010-EC6DR2520359030-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR2520359030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3915.9 lumens
Efficiency: N/A
Efficacy: 156.0 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790722

CATALOG NUMBER: LER6D25D010-EC6DR2520359030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P790722

CATALOG NUMBER: LER6D25D010-EC6DR2520359030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																																				
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																																				
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82																																				
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																																				
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1622763
5°	1511397
10°	1078120
15°	634971
20°	395084
25°	216820
30°	99164
35°	37547
40°	17001
45°	10229
50°	4249
55°	2743
60°	1901
65°	1293
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10229 cd/sqm



TEST NUMBER: P790722

CATALOG NUMBER: LER6D25D010-EC6DR2520359030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1184.3	30.2
10°-20°	1604.1	41.0
20°-30°	848.8	21.7
30°-40°	209.5	5.4
40°-50°	51.1	1.3
50°-60°	13.4	0.3
60°-70°	4.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3637.2	92.9
0°-40°	3846.7	98.2
0°-60°	3911.3	99.9
0°-90°	3915.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3915.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14852	
5°	13780	###
15°	5614	1604
25°	1798	849
35°	282	210
45°	66	51
55°	14	13
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790722

CATALOG NUMBER: LER6D25D010-EC6DR2520359030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	14852.2
2.5°	14608.1
5°	13780.3
7.5°	12117.2
10°	9717.5
12.5°	7345.9
15°	5613.5
17.5°	4374.9
20°	3397.9
22.5°	2548.3
25°	1798.5
27.5°	1206.1
30°	786.0
32.5°	478.2
35°	281.5
37.5°	172.3
40°	119.2
42.5°	91.1
45°	66.2
47.5°	40.0
50°	25.0
52.5°	18.1
55°	14.4
57.5°	11.2
60°	8.7
62.5°	6.9
65°	5.0
67.5°	1.9
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)