

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792128

Luminaire Tested: LER6D35BD010-EC6DR6020359040-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR6020359040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4033.9 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792128

CATALOG NUMBER: LER6D35BD010-EC6DR6020359040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P792128

CATALOG NUMBER: LER6D35BD010-EC6DR6020359040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	523446
5°	536315
10°	542794
15°	517083
20°	455918
25°	368756
30°	249438
35°	124993
40°	20282
45°	19840
50°	20245
55°	20554
60°	21109
65°	21588
70°	22106
75°	22374
80°	21582
85°	17927

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 22374 cd/sqm



TEST NUMBER: P792128

CATALOG NUMBER: LER6D35BD010-EC6DR6020359040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	467.4	11.6
10°-20°	1264.5	31.3
20°-30°	1360.5	33.7
30°-40°	591.4	14.7
40°-50°	99.3	2.5
50°-60°	96.6	2.4
60°-70°	82.6	2.0
70°-80°	55.3	1.4
80°-90°	16.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3092.3	76.7
0°-40°	3683.6	91.3
0°-60°	3879.6	96.2
0°-90°	4033.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4033.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4791	
5°	4890	467
15°	4571	1264
25°	3059	1360
35°	937	591
45°	128	99
55°	108	97
65°	84	83
75°	53	55
85°	14	17
90°	0	



TEST NUMBER: P792128

CATALOG NUMBER: LER6D35BD010-EC6DR6020359040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4790.8
2.5°	4925.5
5°	4889.9
7.5°	4901.2
10°	4892.4
12.5°	4791.4
15°	4571.3
17.5°	4275.8
20°	3921.1
22.5°	3541.4
25°	3058.8
27.5°	2446.5
30°	1977.1
32.5°	1523.8
35°	937.1
37.5°	400.9
40°	142.2
42.5°	130.9
45°	128.4
47.5°	124.1
50°	119.1
52.5°	113.5
55°	107.9
57.5°	102.3
60°	96.6
62.5°	90.4
65°	83.5
67.5°	76.7
70°	69.2
72.5°	61.1
75°	53.0
77.5°	43.6
80°	34.3
82.5°	24.3
85°	14.3
87.5°	5.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)