

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792172

Luminaire Tested: LER6D35BD010-EC6DR6520359035-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P792172
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR6520359035-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3544.5 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P792172
CATALOG NUMBER: LER6D35BD010-EC6DR6520359035-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P792172

CATALOG NUMBER: LER6D35BD010-EC6DR6520359035-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187961
5°	187489
10°	187332
15°	181556
20°	165281
25°	144033
30°	119799
35°	94919
40°	68510
45°	43280
50°	22561
55°	11995
60°	6296
65°	3469
70°	1451
75°	1602
80°	1110
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43280 cd/sqm



TEST NUMBER: P792172

CATALOG NUMBER: LER6D35BD010-EC6DR6520359035-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.4	8.6
10°-20°	833.4	23.5
20°-30°	1018.7	28.7
30°-40°	826.6	23.3
40°-50°	411.9	11.6
50°-60°	114.9	3.2
60°-70°	26.1	0.7
70°-80°	6.8	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2156.5	60.8
0°-40°	2983.1	84.2
0°-60°	3509.9	99.0
0°-90°	3544.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3544.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3218	
5°	3198	304
15°	3003	833
25°	2235	1019
35°	1331	827
45°	524	412
55°	118	115
65°	25	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P792172

CATALOG NUMBER: LER6D35BD010-EC6DR6520359035-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3218.3
2.5°	3216.0
5°	3198.0
7.5°	3187.6
10°	3158.8
12.5°	3100.1
15°	3002.7
17.5°	2850.4
20°	2659.3
22.5°	2453.1
25°	2235.1
27.5°	2001.9
30°	1776.4
32.5°	1553.6
35°	1331.3
37.5°	1109.5
40°	898.6
42.5°	700.9
45°	524.0
47.5°	365.1
50°	248.3
52.5°	171.2
55°	117.8
57.5°	79.5
60°	53.9
62.5°	37.4
65°	25.1
67.5°	12.8
70°	8.5
72.5°	8.0
75°	7.1
77.5°	4.7
80°	3.3
82.5°	2.4
85°	1.4
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)