

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792193

Luminaire Tested: LER6D35BD010-EC6DR7020359024-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR7020359024-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3453.7 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792193

CATALOG NUMBER: LER6D35BD010-EC6DR7020359024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P792193

CATALOG NUMBER: LER6D35BD010-EC6DR7020359024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	424260
5°	411655
10°	400172
15°	394930
20°	368783
25°	277050
30°	195844
35°	69372
40°	36485
45°	38846
50°	40234
55°	40994
60°	41235
65°	40383
70°	38111
75°	35292
80°	31335
85°	25449

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 41260 cd/sqm



TEST NUMBER: P792193

CATALOG NUMBER: LER6D35BD010-EC6DR7020359024-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.0	10.3
10°-20°	971.0	28.1
20°-30°	1069.5	31.0
30°-40°	408.6	11.8
40°-50°	192.9	5.6
50°-60°	191.8	5.6
60°-70°	153.6	4.4
70°-80°	88.3	2.6
80°-90°	24.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2394.5	69.3
0°-40°	2803.2	81.2
0°-60°	3187.9	92.3
0°-90°	3453.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3453.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3883	
5°	3753	354
15°	3491	971
25°	2298	1069
35°	520	409
45°	251	193
55°	215	192
65°	156	154
75°	84	88
85°	20	24
90°	0	



TEST NUMBER: P792193

CATALOG NUMBER: LER6D35BD010-EC6DR7020359024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3883.0
2.5°	3842.4
5°	3753.3
7.5°	3678.9
10°	3606.9
12.5°	3546.1
15°	3491.4
17.5°	3359.2
20°	3171.7
22.5°	2767.1
25°	2298.1
27.5°	2000.5
30°	1552.3
32.5°	1002.7
35°	520.1
37.5°	281.0
40°	255.8
42.5°	253.9
45°	251.4
47.5°	245.9
50°	236.7
52.5°	226.2
55°	215.2
57.5°	202.9
60°	188.7
62.5°	172.8
65°	156.2
67.5°	137.7
70°	119.3
72.5°	100.8
75°	83.6
77.5°	65.8
80°	49.8
82.5°	35.0
85°	20.3
87.5°	8.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)