

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792202

Luminaire Tested: LER6D35BD010-EC6DR7020359027-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR7020359027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2910.4 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P792202
CATALOG NUMBER: LER6D35BD010-EC6DR7020359027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P792202

CATALOG NUMBER: LER6D35BD010-EC6DR7020359027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	357512
5°	346890
10°	337221
15°	332796
20°	310762
25°	233457
30°	165034
35°	58462
40°	30737
45°	32742
50°	33911
55°	34536
60°	34745
65°	34023
70°	32105
75°	29762
80°	26427
85°	21437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 34773 cd/sqm



TEST NUMBER: P792202

CATALOG NUMBER: LER6D35BD010-EC6DR7020359027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.3	10.3
10°-20°	818.3	28.1
20°-30°	901.2	31.0
30°-40°	344.3	11.8
40°-50°	162.6	5.6
50°-60°	161.6	5.6
60°-70°	129.4	4.4
70°-80°	74.4	2.6
80°-90°	20.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2017.8	69.3
0°-40°	2362.2	81.2
0°-60°	2686.4	92.3
0°-90°	2910.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2910.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3272	
5°	3163	298
15°	2942	818
25°	1936	901
35°	438	344
45°	212	163
55°	181	162
65°	132	129
75°	70	74
85°	17	20
90°	0	



TEST NUMBER: P792202

CATALOG NUMBER: LER6D35BD010-EC6DR7020359027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3272.1
2.5°	3237.9
5°	3162.8
7.5°	3100.1
10°	3039.5
12.5°	2988.2
15°	2942.1
17.5°	2830.7
20°	2672.7
22.5°	2331.8
25°	1936.5
27.5°	1685.8
30°	1308.1
32.5°	845.0
35°	438.3
37.5°	236.8
40°	215.5
42.5°	214.0
45°	211.9
47.5°	207.2
50°	199.5
52.5°	190.6
55°	181.3
57.5°	171.0
60°	159.0
62.5°	145.6
65°	131.6
67.5°	116.0
70°	100.5
72.5°	85.0
75°	70.5
77.5°	55.4
80°	42.0
82.5°	29.5
85°	17.1
87.5°	6.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)