

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792210

Luminaire Tested: LER6D35BD010-EC6DR7020359030-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR7020359030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2998.3 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792210

CATALOG NUMBER: LER6D35BD010-EC6DR7020359030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P792210

CATALOG NUMBER: LER6D35BD010-EC6DR7020359030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	368318
5°	357375
10°	347406
15°	342852
20°	320157
25°	240509
30°	170018
35°	60222
40°	31664
45°	33731
50°	34931
55°	35584
60°	35816
65°	35057
70°	33064
75°	30648
80°	27182
85°	22064

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 35816 cd/sqm



TEST NUMBER: P792210

CATALOG NUMBER: LER6D35BD010-EC6DR7020359030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.3	10.3
10°-20°	843.0	28.1
20°-30°	928.4	31.0
30°-40°	354.7	11.8
40°-50°	167.5	5.6
50°-60°	166.5	5.6
60°-70°	133.3	4.4
70°-80°	76.6	2.6
80°-90°	20.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2078.8	69.3
0°-40°	2433.5	81.2
0°-60°	2767.5	92.3
0°-90°	2998.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2998.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3371	
5°	3258	307
15°	3031	843
25°	1995	928
35°	452	355
45°	218	167
55°	187	167
65°	136	133
75°	73	77
85°	18	21
90°	0	



TEST NUMBER: P792210

CATALOG NUMBER: LER6D35BD010-EC6DR7020359030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3371.0
2.5°	3335.7
5°	3258.4
7.5°	3193.8
10°	3131.3
12.5°	3078.5
15°	3031.0
17.5°	2916.2
20°	2753.5
22.5°	2402.3
25°	1995.0
27.5°	1736.7
30°	1347.6
32.5°	870.5
35°	451.5
37.5°	243.9
40°	222.0
42.5°	220.4
45°	218.3
47.5°	213.5
50°	205.5
52.5°	196.4
55°	186.8
57.5°	176.1
60°	163.9
62.5°	150.0
65°	135.6
67.5°	119.6
70°	103.5
72.5°	87.5
75°	72.6
77.5°	57.1
80°	43.2
82.5°	30.4
85°	17.6
87.5°	6.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)