

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792222

Luminaire Tested: LER6D35BD010-EC6DR7020359035-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792222  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D35BD010-EC6DR7020359035-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3877.3 lumens  
Efficiency: N/A  
Efficacy: 125.9 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P792222

CATALOG NUMBER: LER6D35BD010-EC6DR7020359035-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P792222  
 CATALOG NUMBER: LER6D35BD010-EC6DR7020359035-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																											
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																											
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78																											
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71																											
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65																											
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60																											
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56																											
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51																											
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48																											
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	334371
5°	333531
10°	332817
15°	332717
20°	329471
25°	309491
30°	275919
35°	219988
40°	146067
45°	87334
50°	45283
55°	23792
60°	8413
65°	155
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 87334 cd/sqm



TEST NUMBER: P792222

CATALOG NUMBER: LER6D35BD010-EC6DR7020359035-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	289.2	7.5
10°-20°	829.4	21.4
20°-30°	1170.1	30.2
30°-40°	1010.1	26.1
40°-50°	452.3	11.7
50°-60°	118.4	3.1
60°-70°	7.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2288.7	59.0
0°-40°	3298.8	85.1
0°-60°	3869.6	99.8
0°-90°	3877.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3877.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3060	
5°	3041	289
15°	2941	829
25°	2567	1170
35°	1649	1010
45°	565	452
55°	125	118
65°	1	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P792222  
CATALOG NUMBER: LER6D35BD010-EC6DR7020359035-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3060.3
2.5°	3057.0
5°	3041.0
7.5°	3027.8
10°	2999.8
12.5°	2974.5
15°	2941.4
17.5°	2903.5
20°	2833.6
22.5°	2718.6
25°	2567.2
27.5°	2391.7
30°	2187.0
32.5°	1936.6
35°	1649.3
37.5°	1332.3
40°	1024.1
42.5°	778.1
45°	565.2
47.5°	389.6
50°	266.4
52.5°	183.8
55°	124.9
57.5°	75.4
60°	38.5
62.5°	12.1
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)