

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792223

Luminaire Tested: LER6D35BD010-EC6DR7020359040-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792223  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D35BD010-EC6DR7020359040-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2362.5 lumens  
Efficiency: N/A  
Efficacy: 76.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P792223

CATALOG NUMBER: LER6D35BD010-EC6DR7020359040-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P792223

CATALOG NUMBER: LER6D35BD010-EC6DR7020359040-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	290197
5°	281577
10°	273727
15°	270141
20°	252254
25°	189502
30°	133960
35°	47458
40°	24946
45°	26577
50°	27520
55°	28040
60°	28211
65°	27611
70°	26068
75°	24147
80°	21456
85°	17425

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 28225 cd/sqm



TEST NUMBER: P792223

CATALOG NUMBER: LER6D35BD010-EC6DR7020359040-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	242.1	10.2
10°-20°	664.2	28.1
20°-30°	731.5	31.0
30°-40°	279.5	11.8
40°-50°	132.0	5.6
50°-60°	131.2	5.6
60°-70°	105.1	4.4
70°-80°	60.4	2.6
80°-90°	16.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1637.9	69.3
0°-40°	1917.4	81.2
0°-60°	2180.6	92.3
0°-90°	2362.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2362.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2656	
5°	2567	242
15°	2388	664
25°	1572	732
35°	356	280
45°	172	132
55°	147	131
65°	107	105
75°	57	60
85°	14	16
90°	0	



TEST NUMBER: P792223

CATALOG NUMBER: LER6D35BD010-EC6DR7020359040-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2656.0
2.5°	2628.3
5°	2567.3
7.5°	2516.4
10°	2467.2
12.5°	2425.6
15°	2388.2
17.5°	2297.8
20°	2169.5
22.5°	1892.8
25°	1571.9
27.5°	1368.4
30°	1061.8
32.5°	685.9
35°	355.8
37.5°	192.2
40°	174.9
42.5°	173.7
45°	172.0
47.5°	168.2
50°	161.9
52.5°	154.8
55°	147.2
57.5°	138.8
60°	129.1
62.5°	118.2
65°	106.8
67.5°	94.2
70°	81.6
72.5°	69.0
75°	57.2
77.5°	45.0
80°	34.1
82.5°	24.0
85°	13.9
87.5°	5.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)