

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791092

Luminaire Tested: LER6D25D010-EC6DR6520359024-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791092  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D25D010-EC6DR6520359024-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3982.5 lumens  
Efficiency: N/A  
Efficacy: 158.7 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P791092

CATALOG NUMBER: LER6D25D010-EC6DR6520359024-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P791092

CATALOG NUMBER: LER6D25D010-EC6DR6520359024-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	211188
5°	210653
10°	210473
15°	203988
20°	185704
25°	161832
30°	134595
35°	106647
40°	76973
45°	48632
50°	25350
55°	13471
60°	7079
65°	3897
70°	1639
75°	1805
80°	1244
85°	1072

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 48632 cd/sqm



TEST NUMBER: P791092

CATALOG NUMBER: LER6D25D010-EC6DR6520359024-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	342.0	8.6
10°-20°	936.4	23.5
20°-30°	1144.6	28.7
30°-40°	928.7	23.3
40°-50°	462.8	11.6
50°-60°	129.1	3.2
60°-70°	29.3	0.7
70°-80°	7.6	0.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2423.0	60.8
0°-40°	3351.7	84.2
0°-60°	3943.6	99.0
0°-90°	3982.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3982.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3616	
5°	3593	342
15°	3374	936
25°	2511	1145
35°	1496	929
45°	589	463
55°	132	129
65°	28	29
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P791092

CATALOG NUMBER: LER6D25D010-EC6DR6520359024-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3616.0
2.5°	3613.3
5°	3593.1
7.5°	3581.4
10°	3549.0
12.5°	3483.1
15°	3373.7
17.5°	3202.6
20°	2987.9
22.5°	2756.2
25°	2511.3
27.5°	2249.3
30°	1995.8
32.5°	1745.6
35°	1495.8
37.5°	1246.6
40°	1009.6
42.5°	787.5
45°	588.8
47.5°	410.2
50°	279.0
52.5°	192.4
55°	132.3
57.5°	89.3
60°	60.6
62.5°	42.0
65°	28.2
67.5°	14.3
70°	9.6
72.5°	9.0
75°	8.0
77.5°	5.3
80°	3.7
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)