

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792371

Luminaire Tested: LER6D40BD010-EC6DR3540509040-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792371  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D40BD010-EC6DR3540509040-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4429.5 lumens  
Efficiency: N/A  
Efficacy: 125.8 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P792371  
CATALOG NUMBER: LER6D40BD010-EC6DR3540509040-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P792371

CATALOG NUMBER: LER6D40BD010-EC6DR3540509040-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	98	96	96	95	93	92																
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	95	93	92	92	91	89	88	88	84																
	2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	91	89	88	88	86	84	82	81	81																
	3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88	88	86	84	82	81	81	79	78	78	75																
	4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84	82	81	81	79	78	78	76	75	75	72																
	5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81	81	79	78	78	76	75	75	72	72	70																
	6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78	78	76	75	75	73	72	72	70	70	68																
	7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75	75	73	72	72	70	70	68	68	66	64																
	8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72	72	70	69	69	67	66	64	64	62	60																
	9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70	70	68	67	67	65	64	62	62	60	58																
	10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68	68	66	65	65	63	62	60	60	58	56																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1331637
5°	1300355
10°	1171959
15°	909626
20°	515926
25°	200726
30°	74878
35°	41042
40°	26829
45°	16333
50°	10386
55°	7334
60°	5376
65°	2921
70°	224
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16333 cd/sqm



TEST NUMBER: P792371

CATALOG NUMBER: LER6D40BD010-EC6DR3540509040-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1090.4	24.6
10°-20°	2128.9	48.1
20°-30°	868.3	19.6
30°-40°	207.8	4.7
40°-50°	86.6	2.0
50°-60°	35.8	0.8
60°-70°	11.2	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4087.6	92.3
0°-40°	4295.4	97.0
0°-60°	4417.8	99.7
0°-90°	4429.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4429.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12188	
5°	11856	###
15°	8042	2129
25°	1665	868
35°	308	208
45°	106	87
55°	38	36
65°	11	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P792371

CATALOG NUMBER: LER6D40BD010-EC6DR3540509040-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	12187.7
2.5°	12114.6
5°	11856.1
7.5°	11340.3
10°	10563.3
12.5°	9469.3
15°	8041.6
17.5°	6295.6
20°	4437.2
22.5°	2829.4
25°	1665.0
27.5°	941.1
30°	593.5
32.5°	416.7
35°	307.7
37.5°	237.9
40°	188.1
42.5°	144.9
45°	105.7
47.5°	79.1
50°	61.1
52.5°	48.5
55°	38.5
57.5°	31.2
60°	24.6
62.5°	17.9
65°	11.3
67.5°	4.0
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)