

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791118

Luminaire Tested: LER6D25D010-EC6DR6520359035-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR6520359035-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4579.1 lumens
Efficiency: N/A
Efficacy: 182.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791118

CATALOG NUMBER: LER6D25D010-EC6DR6520359035-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P791118

CATALOG NUMBER: LER6D25D010-EC6DR6520359035-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	242826
5°	242211
10°	242005
15°	234546
20°	213524
25°	186075
30°	154759
35°	122625
40°	88500
45°	55917
50°	29148
55°	15487
60°	8141
65°	4478
70°	1878
75°	2076
80°	1446
85°	1206

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55917 cd/sqm



TEST NUMBER: P791118

CATALOG NUMBER: LER6D25D010-EC6DR6520359035-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	393.2	8.6
10°-20°	1076.7	23.5
20°-30°	1316.1	28.7
30°-40°	1067.8	23.3
40°-50°	532.1	11.6
50°-60°	148.4	3.2
60°-70°	33.7	0.7
70°-80°	8.8	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2786.0	60.8
0°-40°	3853.8	84.2
0°-60°	4534.3	99.0
0°-90°	4579.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4579.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4158	
5°	4131	393
15°	3879	1077
25°	2888	1316
35°	1720	1068
45°	677	532
55°	152	148
65°	32	34
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P791118

CATALOG NUMBER: LER6D25D010-EC6DR6520359035-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4157.7
2.5°	4154.6
5°	4131.4
7.5°	4118.0
10°	4080.7
12.5°	4004.9
15°	3879.1
17.5°	3682.3
20°	3435.5
22.5°	3169.1
25°	2887.5
27.5°	2586.3
30°	2294.8
32.5°	2007.0
35°	1719.9
37.5°	1433.3
40°	1160.8
42.5°	905.5
45°	677.0
47.5°	471.7
50°	320.8
52.5°	221.2
55°	152.1
57.5°	102.6
60°	69.7
62.5°	48.3
65°	32.4
67.5°	16.5
70°	11.0
72.5°	10.4
75°	9.2
77.5°	6.1
80°	4.3
82.5°	3.1
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)