

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791162

Luminaire Tested: LER6D25D010-EC6DR7020359035-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791162
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR7020359035-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4119.2 lumens
Efficiency: N/A
Efficacy: 164.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791162
CATALOG NUMBER: LER6D25D010-EC6DR7020359035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P791162

CATALOG NUMBER: LER6D25D010-EC6DR7020359035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																	
	1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91	91	91	91	91	91	91	91	91	91	91																	
	2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83	83	83	83	83	83	83	83	83	83	83																	
	3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76	76	76	76	76	76	76	76	76	76	76																	
	4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70	70	70	70	70	70	70	70																	
	5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65	65	65	65	65	65	65	65	65	65	65																	
	6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61	61	61	61	61	61	61	61	61	61	61																	
	7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57	57	57	57	57	57	57	57																	
	8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53	53	53	53	53	53	53	53																	
	9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50	50	50	50	50	50	50	50	50	50	50																	
	10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	48	48	48	48	48	48	48	48	48	48																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	506008
5°	490974
10°	477291
15°	471034
20°	439849
25°	330432
30°	233592
35°	82737
40°	43502
45°	46340
50°	47985
55°	48880
60°	49189
65°	48139
70°	45459
75°	42088
80°	37375
85°	30338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 49211 cd/sqm



TEST NUMBER: P791162

CATALOG NUMBER: LER6D25D010-EC6DR7020359035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	422.2	10.3
10°-20°	1158.2	28.1
20°-30°	1275.6	31.0
30°-40°	487.3	11.8
40°-50°	230.1	5.6
50°-60°	228.8	5.6
60°-70°	183.1	4.4
70°-80°	105.3	2.6
80°-90°	28.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2856.0	69.3
0°-40°	3343.3	81.2
0°-60°	3802.2	92.3
0°-90°	4119.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4119.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4631	
5°	4476	422
15°	4164	1158
25°	2741	1276
35°	620	487
45°	300	230
55°	257	229
65°	186	183
75°	100	105
85°	24	29
90°	0	



TEST NUMBER: P791162

CATALOG NUMBER: LER6D25D010-EC6DR7020359035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4631.2
2.5°	4582.8
5°	4476.5
7.5°	4387.8
10°	4302.0
12.5°	4229.4
15°	4164.2
17.5°	4006.5
20°	3782.9
22.5°	3300.4
25°	2740.9
27.5°	2386.0
30°	1851.5
32.5°	1195.9
35°	620.3
37.5°	335.1
40°	305.0
42.5°	302.8
45°	299.9
47.5°	293.3
50°	282.3
52.5°	269.8
55°	256.6
57.5°	242.0
60°	225.1
62.5°	206.0
65°	186.2
67.5°	164.2
70°	142.3
72.5°	120.3
75°	99.7
77.5°	78.5
80°	59.4
82.5°	41.8
85°	24.2
87.5°	9.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)