

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792506

Luminaire Tested: LER6D40BD010-EC6DR5040509035-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P792506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR5040509035-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4463.4 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792506

CATALOG NUMBER: LER6D40BD010-EC6DR5040509035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P792506

CATALOG NUMBER: LER6D40BD010-EC6DR5040509035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95					95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90					90			
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85					85			
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80					80			
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76					76			
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72					72			
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69					69			
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65					65			
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62					62			
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59					59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	785771
5°	777530
10°	764731
15°	696348
20°	579446
25°	411313
30°	217708
35°	88713
40°	32947
45°	15081
50°	6187
55°	3238
60°	1595
65°	465
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15081 cd/sqm



TEST NUMBER: P792506

CATALOG NUMBER: LER6D40BD010-EC6DR5040509035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	670.1	15.0
10°-20°	1693.4	37.9
20°-30°	1521.1	34.1
30°-40°	476.3	10.7
40°-50°	83.4	1.9
50°-60°	16.6	0.4
60°-70°	2.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3884.6	87.0
0°-40°	4360.9	97.7
0°-60°	4460.9	99.9
0°-90°	4463.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4463.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7192	
5°	7089	670
15°	6156	1693
25°	3412	1521
35°	665	476
45°	98	83
55°	17	17
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P792506

CATALOG NUMBER: LER6D40BD010-EC6DR5040509035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7191.7
2.5°	7155.9
5°	7089.2
7.5°	6987.4
10°	6892.8
12.5°	6589.6
15°	6156.1
17.5°	5605.6
20°	4983.5
22.5°	4263.7
25°	3411.8
27.5°	2508.4
30°	1725.6
32.5°	1123.5
35°	665.1
37.5°	382.0
40°	231.0
42.5°	150.4
45°	97.6
47.5°	59.4
50°	36.4
52.5°	24.9
55°	17.0
57.5°	11.5
60°	7.3
62.5°	4.2
65°	1.8
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)