

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792576

Luminaire Tested: LER6D40BD010-EC6DR6040509024-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792576  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D40BD010-EC6DR6040509024-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3847.0 lumens  
Efficiency: N/A  
Efficacy: 109.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P792576

CATALOG NUMBER: LER6D40BD010-EC6DR6040509024-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P792576

CATALOG NUMBER: LER6D40BD010-EC6DR6040509024-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	499180
5°	511451
10°	517631
15°	493114
20°	434779
25°	351662
30°	237869
35°	119191
40°	19341
45°	18928
50°	19310
55°	19601
60°	20148
65°	20605
70°	21084
75°	21319
80°	20575
85°	17175

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 21319 cd/sqm



TEST NUMBER: P792576

CATALOG NUMBER: LER6D40BD010-EC6DR6040509024-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	445.7	11.6
10°-20°	1205.8	31.3
20°-30°	1297.4	33.7
30°-40°	563.9	14.7
40°-50°	94.7	2.5
50°-60°	92.1	2.4
60°-70°	78.8	2.0
70°-80°	52.7	1.4
80°-90°	15.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2948.9	76.7
0°-40°	3512.8	91.3
0°-60°	3699.7	96.2
0°-90°	3847.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3847.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4569	
5°	4663	446
15°	4359	1206
25°	2917	1297
35°	894	564
45°	122	95
55°	103	92
65°	80	79
75°	50	53
85°	14	16
90°	0	



TEST NUMBER: P792576

CATALOG NUMBER: LER6D40BD010-EC6DR6040509024-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4568.7
2.5°	4697.1
5°	4663.2
7.5°	4673.9
10°	4665.6
12.5°	4569.3
15°	4359.4
17.5°	4077.6
20°	3739.3
22.5°	3377.2
25°	2917.0
27.5°	2333.1
30°	1885.4
32.5°	1453.1
35°	893.6
37.5°	382.3
40°	135.6
42.5°	124.9
45°	122.5
47.5°	118.3
50°	113.6
52.5°	108.2
55°	102.9
57.5°	97.5
60°	92.2
62.5°	86.2
65°	79.7
67.5°	73.1
70°	66.0
72.5°	58.3
75°	50.5
77.5°	41.6
80°	32.7
82.5°	23.2
85°	13.7
87.5°	4.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)