

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792586

Luminaire Tested: LER6D40BD010-EC6DR6040509027-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR6040509027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3946.3 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P792586
CATALOG NUMBER: LER6D40BD010-EC6DR6040509027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P792586

CATALOG NUMBER: LER6D40BD010-EC6DR6040509027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	512083
5°	524678
10°	531022
15°	505862
20°	446023
25°	360751
30°	244013
35°	122285
40°	19840
45°	19407
50°	19803
55°	20097
60°	20650
65°	21122
70°	21627
75°	21867
80°	21078
85°	17551

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 21867 cd/sqm



TEST NUMBER: P792586

CATALOG NUMBER: LER6D40BD010-EC6DR6040509027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	457.2	11.6
10°-20°	1237.0	31.3
20°-30°	1330.9	33.7
30°-40°	578.5	14.7
40°-50°	97.2	2.5
50°-60°	94.5	2.4
60°-70°	80.8	2.0
70°-80°	54.1	1.4
80°-90°	16.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3025.2	76.7
0°-40°	3603.7	91.3
0°-60°	3795.3	96.2
0°-90°	3946.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3946.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4687	
5°	4784	457
15°	4472	1237
25°	2992	1331
35°	917	579
45°	126	97
55°	106	94
65°	82	81
75°	52	54
85°	14	16
90°	0	



TEST NUMBER: P792586

CATALOG NUMBER: LER6D40BD010-EC6DR6040509027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4686.8
2.5°	4818.6
5°	4783.8
7.5°	4794.8
10°	4786.3
12.5°	4687.4
15°	4472.1
17.5°	4183.0
20°	3836.0
22.5°	3464.5
25°	2992.4
27.5°	2393.4
30°	1934.1
32.5°	1490.7
35°	916.8
37.5°	392.2
40°	139.1
42.5°	128.1
45°	125.6
47.5°	121.4
50°	116.5
52.5°	111.0
55°	105.5
57.5°	100.0
60°	94.5
62.5°	88.4
65°	81.7
67.5°	75.0
70°	67.7
72.5°	59.8
75°	51.8
77.5°	42.7
80°	33.5
82.5°	23.8
85°	14.0
87.5°	4.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)