

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791259

Luminaire Tested: LER6D30D010-EC6DR2015309035-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791259  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D30D010-EC6DR2015309035-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3511.9 lumens  
Efficiency: N/A  
Efficacy: 121.1 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P791259

CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P791259

CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	93	92															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	91	89															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	88	86															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	86	84															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	84	82															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	82	80															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	80	78															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	78	76															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2183970
5°	1970345
10°	1105868
15°	562137
20°	237999
25°	109863
30°	58161
35°	31345
40°	16759
45°	9905
50°	5745
55°	3048
60°	1945
65°	1370
70°	575
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9905 cd/sqm



TEST NUMBER: P791259

CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1423.2	40.5
10°-20°	1401.4	39.9
20°-30°	457.8	13.0
30°-40°	155.9	4.4
40°-50°	52.4	1.5
50°-60°	15.8	0.4
60°-70°	5.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3282.3	93.5
0°-40°	3438.2	97.9
0°-60°	3506.4	99.8
0°-90°	3511.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3511.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	19989	
5°	17965	###
15°	4970	1401
25°	911	458
35°	235	156
45°	64	52
55°	16	16
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791259  
CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	19988.6
0.5°	19988.6
1°	19963.7
1.5°	19913.8
2°	19823.0
2.5°	19702.0
3°	19531.1
3.5°	19292.6
4°	18938.4
4.5°	18507.7
5°	17964.8
5.5°	17251.1
6°	16519.5
6.5°	15681.2
7°	14860.6
7.5°	13899.4
8°	13041.5
8.5°	12178.3
9°	11380.9
9.5°	10649.3
10°	9967.6
12.5°	7157.1
15°	4969.6
17.5°	3246.6
20°	2046.9
22.5°	1326.0
25°	911.3
27.5°	640.8
30°	461.0
32.5°	331.1
35°	235.0
37.5°	163.8
40°	117.5
42.5°	85.4
45°	64.1
47.5°	49.8
50°	33.8
52.5°	21.4
55°	16.0
57.5°	12.5
60°	8.9
62.5°	7.1
65°	5.3



TEST NUMBER: P791259  
CATALOG NUMBER: LER6D30D010-EC6DR2015309035-6LBS1B

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.6
70°		1.8

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)