

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792609

Luminaire Tested: LER6D40BD010-EC6DR6040509040-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR6040509040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4986.2 lumens
Efficiency: N/A
Efficacy: 141.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792609

CATALOG NUMBER: LER6D40BD010-EC6DR6040509040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P792609

CATALOG NUMBER: LER6D40BD010-EC6DR6040509040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	647020
5°	662927
10°	670937
15°	639157
20°	563540
25°	455810
30°	308318
35°	154497
40°	25060
45°	24537
50°	25021
55°	25392
60°	26113
65°	26706
70°	27314
75°	27651
80°	26678
85°	22189

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 27651 cd/sqm



TEST NUMBER: P792609

CATALOG NUMBER: LER6D40BD010-EC6DR6040509040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	577.7	11.6
10°-20°	1563.0	31.3
20°-30°	1681.6	33.7
30°-40°	731.0	14.7
40°-50°	122.8	2.5
50°-60°	119.4	2.4
60°-70°	102.1	2.0
70°-80°	68.3	1.4
80°-90°	20.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3822.3	76.7
0°-40°	4553.2	91.3
0°-60°	4795.4	96.2
0°-90°	4986.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4986.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5922	
5°	6044	578
15°	5650	1563
25°	3781	1682
35°	1158	731
45°	159	123
55°	133	119
65°	103	102
75°	66	68
85°	18	20
90°	0	



TEST NUMBER: P792609

CATALOG NUMBER: LER6D40BD010-EC6DR6040509040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5921.8
2.5°	6088.2
5°	6044.3
7.5°	6058.2
10°	6047.4
12.5°	5922.5
15°	5650.5
17.5°	5285.2
20°	4846.7
22.5°	4377.4
25°	3780.9
27.5°	3024.1
30°	2443.8
32.5°	1883.5
35°	1158.3
37.5°	495.5
40°	175.7
42.5°	161.8
45°	158.8
47.5°	153.4
50°	147.2
52.5°	140.3
55°	133.3
57.5°	126.4
60°	119.5
62.5°	111.7
65°	103.3
67.5°	94.8
70°	85.5
72.5°	75.5
75°	65.5
77.5°	53.9
80°	42.4
82.5°	30.1
85°	17.7
87.5°	6.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)