

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792636

Luminaire Tested: LER6D40BD010-EC6DR6540509027-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P792636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR6540509027-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4008.0 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P792636
CATALOG NUMBER: LER6D40BD010-EC6DR6540509027-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P792636

CATALOG NUMBER: LER6D40BD010-EC6DR6540509027-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	212543
5°	212007
10°	211825
15°	205294
20°	186898
25°	162870
30°	135458
35°	107332
40°	77468
45°	48938
50°	25514
55°	13563
60°	7125
65°	3911
70°	1639
75°	1805
80°	1244
85°	1072

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 48938 cd/sqm



TEST NUMBER: P792636

CATALOG NUMBER: LER6D40BD010-EC6DR6540509027-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	344.2	8.6
10°-20°	942.4	23.5
20°-30°	1152.0	28.7
30°-40°	934.7	23.3
40°-50°	465.8	11.6
50°-60°	129.9	3.2
60°-70°	29.5	0.7
70°-80°	7.7	0.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2438.5	60.8
0°-40°	3373.2	84.2
0°-60°	3968.9	99.0
0°-90°	4008.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4008.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3639	
5°	3616	344
15°	3395	942
25°	2527	1152
35°	1505	935
45°	592	466
55°	133	130
65°	28	29
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P792636

CATALOG NUMBER: LER6D40BD010-EC6DR6540509027-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3639.2
2.5°	3636.5
5°	3616.2
7.5°	3604.4
10°	3571.8
12.5°	3505.5
15°	3395.3
17.5°	3223.1
20°	3007.1
22.5°	2773.9
25°	2527.4
27.5°	2263.7
30°	2008.6
32.5°	1756.8
35°	1505.4
37.5°	1254.6
40°	1016.1
42.5°	792.5
45°	592.5
47.5°	412.9
50°	280.8
52.5°	193.6
55°	133.2
57.5°	89.8
60°	61.0
62.5°	42.2
65°	28.3
67.5°	14.4
70°	9.6
72.5°	9.1
75°	8.0
77.5°	5.3
80°	3.7
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)