

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792638

Luminaire Tested: LER6D40BD010-EC6DR6540509027-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P792638
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR6540509027-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3808.5 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792638

CATALOG NUMBER: LER6D40BD010-EC6DR6540509027-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P792638

CATALOG NUMBER: LER6D40BD010-EC6DR6540509027-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201961
5°	201454
10°	201281
15°	195075
20°	177593
25°	154763
30°	128721
35°	101992
40°	73611
45°	46501
50°	24242
55°	12881
60°	6763
65°	3717
70°	1554
75°	1715
80°	1211
85°	1005

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 46501 cd/sqm



TEST NUMBER: P792638

CATALOG NUMBER: LER6D40BD010-EC6DR6540509027-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.0	8.6
10°-20°	895.5	23.5
20°-30°	1094.6	28.7
30°-40°	888.1	23.3
40°-50°	442.6	11.6
50°-60°	123.5	3.2
60°-70°	28.0	0.7
70°-80°	7.3	0.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2317.2	60.8
0°-40°	3205.3	84.2
0°-60°	3771.3	99.0
0°-90°	3808.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3808.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3458	
5°	3436	327
15°	3226	896
25°	2402	1095
35°	1430	888
45°	563	443
55°	126	123
65°	27	28
75°	8	7
85°	2	2
90°	0	



TEST NUMBER: P792638

CATALOG NUMBER: LER6D40BD010-EC6DR6540509027-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3458.0
2.5°	3455.5
5°	3436.2
7.5°	3425.0
10°	3394.0
12.5°	3331.0
15°	3226.3
17.5°	3062.7
20°	2857.4
22.5°	2635.8
25°	2401.6
27.5°	2151.1
30°	1908.7
32.5°	1669.3
35°	1430.5
37.5°	1192.1
40°	965.5
42.5°	753.1
45°	563.0
47.5°	392.3
50°	266.8
52.5°	184.0
55°	126.5
57.5°	85.4
60°	57.9
62.5°	40.1
65°	26.9
67.5°	13.7
70°	9.1
72.5°	8.6
75°	7.6
77.5°	5.1
80°	3.6
82.5°	2.5
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)