

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792642

Luminaire Tested: LER6D40BD010-EC6DR6540509030-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR6540509030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3384.5 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792642

CATALOG NUMBER: LER6D40BD010-EC6DR6540509030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P792642

CATALOG NUMBER: LER6D40BD010-EC6DR6540509030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	364090
5°	364384
10°	377217
15°	377838
20°	347865
25°	296399
30°	226905
35°	160299
40°	94621
45°	38413
50°	13921
55°	7753
60°	4458
65°	2456
70°	2588
75°	1984
80°	2076
85°	1755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38413 cd/sqm



TEST NUMBER: P792642

CATALOG NUMBER: LER6D40BD010-EC6DR6540509030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	320.9	9.5
10°-20°	925.6	27.3
20°-30°	1110.5	32.8
30°-40°	746.3	22.0
40°-50°	223.4	6.6
50°-60°	39.4	1.2
60°-70°	11.2	0.3
70°-80°	5.5	0.2
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2356.9	69.6
0°-40°	3103.2	91.7
0°-60°	3366.0	99.5
0°-90°	3384.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3384.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3332	
5°	3322	321
15°	3340	926
25°	2459	1111
35°	1202	746
45°	249	223
55°	41	39
65°	10	11
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P792642

CATALOG NUMBER: LER6D40BD010-EC6DR6540509030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3332.3
2.5°	3346.5
5°	3322.3
7.5°	3372.5
10°	3400.0
12.5°	3393.3
15°	3340.3
17.5°	3210.6
20°	2991.8
22.5°	2734.2
25°	2458.6
27.5°	2147.5
30°	1798.5
32.5°	1482.2
35°	1201.8
37.5°	924.8
40°	663.4
42.5°	433.3
45°	248.6
47.5°	131.6
50°	81.9
52.5°	56.8
55°	40.7
57.5°	29.4
60°	20.4
62.5°	13.3
65°	9.5
67.5°	8.5
70°	8.1
72.5°	6.2
75°	4.7
77.5°	4.3
80°	3.3
82.5°	2.4
85°	1.4
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)