

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792644

Luminaire Tested: LER6D40BD010-EC6DR6540509030-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792644  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D40BD010-EC6DR6540509030-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4129.2 lumens  
Efficiency: N/A  
Efficacy: 117.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P792644

CATALOG NUMBER: LER6D40BD010-EC6DR6540509030-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P792644

CATALOG NUMBER: LER6D40BD010-EC6DR6540509030-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	218968
5°	218415
10°	218224
15°	211498
20°	192547
25°	167793
30°	139551
35°	110576
40°	79809
45°	50416
50°	26277
55°	13970
60°	7336
65°	4035
70°	1691
75°	1873
80°	1312
85°	1139

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 50416 cd/sqm



TEST NUMBER: P792644

CATALOG NUMBER: LER6D40BD010-EC6DR6540509030-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	354.6	8.6
10°-20°	970.9	23.5
20°-30°	1186.8	28.7
30°-40°	962.9	23.3
40°-50°	479.8	11.6
50°-60°	133.8	3.2
60°-70°	30.4	0.7
70°-80°	7.9	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2512.2	60.8
0°-40°	3475.1	84.2
0°-60°	4088.8	99.0
0°-90°	4129.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4129.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3749	
5°	3726	355
15°	3498	971
25°	2604	1187
35°	1551	963
45°	610	480
55°	137	134
65°	29	30
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P792644

CATALOG NUMBER: LER6D40BD010-EC6DR6540509030-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3749.2
2.5°	3746.4
5°	3725.5
7.5°	3713.4
10°	3679.7
12.5°	3611.4
15°	3497.9
17.5°	3320.5
20°	3098.0
22.5°	2857.7
25°	2603.8
27.5°	2332.1
30°	2069.3
32.5°	1809.8
35°	1550.9
37.5°	1292.5
40°	1046.8
42.5°	816.5
45°	610.4
47.5°	425.3
50°	289.2
52.5°	199.4
55°	137.2
57.5°	92.6
60°	62.8
62.5°	43.5
65°	29.2
67.5°	14.9
70°	9.9
72.5°	9.4
75°	8.3
77.5°	5.5
80°	3.9
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)