

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791634

Luminaire Tested: LER6D30D010-EC6DR6020359030-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791634  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D30D010-EC6DR6020359030-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5051.7 lumens  
Efficiency: N/A  
Efficacy: 174.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P791634  
CATALOG NUMBER: LER6D30D010-EC6DR6020359030-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P791634

CATALOG NUMBER: LER6D30D010-EC6DR6020359030-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	655521
5°	671636
10°	679746
15°	647550
20°	570946
25°	461789
30°	312368
35°	156525
40°	25388
45°	24847
50°	25344
55°	25735
60°	26441
65°	27043
70°	27697
75°	28031
80°	26993
85°	22565

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 28031 cd/sqm



TEST NUMBER: P791634

CATALOG NUMBER: LER6D30D010-EC6DR6020359030-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	585.3	11.6
10°-20°	1583.5	31.3
20°-30°	1703.7	33.7
30°-40°	740.5	14.7
40°-50°	124.4	2.5
50°-60°	120.9	2.4
60°-70°	103.4	2.0
70°-80°	69.2	1.4
80°-90°	20.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3872.5	76.7
0°-40°	4613.0	91.3
0°-60°	4858.3	96.2
0°-90°	5051.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5051.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6000	
5°	6124	585
15°	5725	1583
25°	3830	1704
35°	1174	741
45°	161	124
55°	135	121
65°	105	103
75°	66	69
85°	18	21
90°	0	



TEST NUMBER: P791634

CATALOG NUMBER: LER6D30D010-EC6DR6020359030-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5999.6
2.5°	6168.2
5°	6123.7
7.5°	6137.8
10°	6126.8
12.5°	6000.3
15°	5724.7
17.5°	5354.6
20°	4910.4
22.5°	4434.9
25°	3830.5
27.5°	3063.8
30°	2475.9
32.5°	1908.2
35°	1173.5
37.5°	502.0
40°	178.0
42.5°	164.0
45°	160.8
47.5°	155.4
50°	149.1
52.5°	142.1
55°	135.1
57.5°	128.0
60°	121.0
62.5°	113.2
65°	104.6
67.5°	96.0
70°	86.7
72.5°	76.5
75°	66.4
77.5°	54.7
80°	42.9
82.5°	30.5
85°	18.0
87.5°	6.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)