

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791639

Luminaire Tested: LER6D30D010-EC6DR6020359035-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR6020359035-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4637.3 lumens
Efficiency: N/A
Efficacy: 159.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791639

CATALOG NUMBER: LER6D30D010-EC6DR6020359035-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P791639

CATALOG NUMBER: LER6D30D010-EC6DR6020359035-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	601743
5°	616534
10°	623984
15°	594431
20°	524100
25°	423911
30°	286744
35°	143693
40°	23306
45°	22807
50°	23270
55°	23621
60°	24278
65°	24819
70°	25429
75°	25709
80°	24791
85°	20685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 25709 cd/sqm



TEST NUMBER: P791639

CATALOG NUMBER: LER6D30D010-EC6DR6020359035-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	537.3	11.6
10°-20°	1453.6	31.3
20°-30°	1563.9	33.7
30°-40°	679.8	14.7
40°-50°	114.2	2.5
50°-60°	111.0	2.4
60°-70°	95.0	2.0
70°-80°	63.5	1.4
80°-90°	19.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3554.8	76.7
0°-40°	4234.6	91.3
0°-60°	4459.8	96.2
0°-90°	4637.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4637.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5507	
5°	5621	537
15°	5255	1454
25°	3516	1564
35°	1077	680
45°	148	114
55°	124	111
65°	96	95
75°	61	64
85°	16	19
90°	0	



TEST NUMBER: P791639

CATALOG NUMBER: LER6D30D010-EC6DR6020359035-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5507.4
2.5°	5662.2
5°	5621.3
7.5°	5634.2
10°	5624.2
12.5°	5508.1
15°	5255.1
17.5°	4915.4
20°	4507.5
22.5°	4071.0
25°	3516.3
27.5°	2812.5
30°	2272.8
32.5°	1751.7
35°	1077.3
37.5°	460.9
40°	163.4
42.5°	150.5
45°	147.6
47.5°	142.6
50°	136.9
52.5°	130.4
55°	124.0
57.5°	117.5
60°	111.1
62.5°	103.9
65°	96.0
67.5°	88.2
70°	79.6
72.5°	70.2
75°	60.9
77.5°	50.2
80°	39.4
82.5°	28.0
85°	16.5
87.5°	5.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)