

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792649

Luminaire Tested: LER6D40BD010-EC6DR6540509035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792649
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR6540509035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4162.2 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792649

CATALOG NUMBER: LER6D40BD010-EC6DR6540509035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P792649

CATALOG NUMBER: LER6D40BD010-EC6DR6540509035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	447751
5°	448123
10°	463900
15°	464665
20°	427803
25°	364513
30°	279048
35°	197140
40°	116372
45°	47236
50°	17117
55°	9544
60°	5463
65°	2999
70°	3163
75°	2448
80°	2580
85°	2131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 47236 cd/sqm



TEST NUMBER: P792649

CATALOG NUMBER: LER6D40BD010-EC6DR6540509035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	394.6	9.5
10°-20°	1138.2	27.3
20°-30°	1365.7	32.8
30°-40°	917.8	22.1
40°-50°	274.7	6.6
50°-60°	48.5	1.2
60°-70°	13.8	0.3
70°-80°	6.7	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2898.5	69.6
0°-40°	3816.3	91.7
0°-60°	4139.6	99.5
0°-90°	4162.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4162.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4098	
5°	4086	395
15°	4108	1138
25°	3024	1366
35°	1478	918
45°	306	275
55°	50	48
65°	12	14
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P792649

CATALOG NUMBER: LER6D40BD010-EC6DR6540509035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4098.0
2.5°	4115.5
5°	4085.8
7.5°	4147.5
10°	4181.3
12.5°	4173.1
15°	4107.9
17.5°	3948.3
20°	3679.3
22.5°	3362.5
25°	3023.6
27.5°	2641.0
30°	2211.8
32.5°	1822.8
35°	1478.0
37.5°	1137.3
40°	815.9
42.5°	532.9
45°	305.7
47.5°	161.9
50°	100.7
52.5°	69.9
55°	50.1
57.5°	36.1
60°	25.0
62.5°	16.3
65°	11.6
67.5°	10.5
70°	9.9
72.5°	7.6
75°	5.8
77.5°	5.2
80°	4.1
82.5°	2.9
85°	1.7
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)