

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792672

Luminaire Tested: LER6D40BD010-EC6DR7040509024-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR7040509024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3872.1 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792672

CATALOG NUMBER: LER6D40BD010-EC6DR7040509024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P792672

CATALOG NUMBER: LER6D40BD010-EC6DR7040509024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	475656
5°	461525
10°	448656
15°	442766
20°	413455
25°	310612
30°	219575
35°	77775
40°	40892
45°	43559
50°	45113
55°	45946
60°	46239
65°	45269
70°	42711
75°	39556
80°	35110
85°	28457

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 46262 cd/sqm



TEST NUMBER: P792672

CATALOG NUMBER: LER6D40BD010-EC6DR7040509024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	396.9	10.3
10°-20°	1088.7	28.1
20°-30°	1199.0	31.0
30°-40°	458.1	11.8
40°-50°	216.3	5.6
50°-60°	215.0	5.6
60°-70°	172.2	4.4
70°-80°	98.9	2.6
80°-90°	26.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2684.6	69.3
0°-40°	3142.7	81.2
0°-60°	3574.1	92.3
0°-90°	3872.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3872.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4353	
5°	4208	397
15°	3914	1089
25°	2576	1199
35°	583	458
45°	282	216
55°	241	215
65°	175	172
75°	94	99
85°	23	27
90°	0	



TEST NUMBER: P792672

CATALOG NUMBER: LER6D40BD010-EC6DR7040509024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4353.4
2.5°	4307.9
5°	4208.0
7.5°	4124.6
10°	4043.9
12.5°	3975.7
15°	3914.3
17.5°	3766.1
20°	3555.9
22.5°	3102.4
25°	2576.5
27.5°	2242.9
30°	1740.4
32.5°	1124.2
35°	583.1
37.5°	315.0
40°	286.7
42.5°	284.7
45°	281.9
47.5°	275.7
50°	265.4
52.5°	253.6
55°	241.2
57.5°	227.5
60°	211.6
62.5°	193.7
65°	175.1
67.5°	154.4
70°	133.7
72.5°	113.0
75°	93.7
77.5°	73.8
80°	55.8
82.5°	39.3
85°	22.7
87.5°	9.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)