

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791668

Luminaire Tested: LER6D30D010-EC6DR6520359024-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791668
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR6520359024-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4476.2 lumens
Efficiency: N/A
Efficacy: 154.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791668
CATALOG NUMBER: LER6D30D010-EC6DR6520359024-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P791668

CATALOG NUMBER: LER6D30D010-EC6DR6520359024-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	237365
5°	236765
10°	236567
15°	229274
20°	208725
25°	181893
30°	151279
35°	119866
40°	86518
45°	54653
50°	28494
55°	15141
60°	7955
65°	4381
70°	1844
75°	2031
80°	1413
85°	1206

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54653 cd/sqm



TEST NUMBER: P791668

CATALOG NUMBER: LER6D30D010-EC6DR6520359024-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	384.3	8.6
10°-20°	1052.5	23.5
20°-30°	1286.5	28.7
30°-40°	1043.8	23.3
40°-50°	520.2	11.6
50°-60°	145.1	3.2
60°-70°	33.0	0.7
70°-80°	8.6	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2723.3	60.8
0°-40°	3767.2	84.2
0°-60°	4432.4	99.0
0°-90°	4476.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4476.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4064	
5°	4038	384
15°	3792	1052
25°	2823	1287
35°	1681	1044
45°	662	520
55°	149	145
65°	32	33
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P791668

CATALOG NUMBER: LER6D30D010-EC6DR6520359024-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4064.2
2.5°	4061.2
5°	4038.5
7.5°	4025.4
10°	3989.0
12.5°	3914.9
15°	3791.9
17.5°	3599.6
20°	3358.3
22.5°	3097.9
25°	2822.6
27.5°	2528.1
30°	2243.2
32.5°	1961.9
35°	1681.2
37.5°	1401.1
40°	1134.8
42.5°	885.1
45°	661.7
47.5°	461.1
50°	313.6
52.5°	216.2
55°	148.7
57.5°	100.3
60°	68.1
62.5°	47.2
65°	31.7
67.5°	16.1
70°	10.8
72.5°	10.2
75°	9.0
77.5°	6.0
80°	4.2
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)