

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792688

Luminaire Tested: LER6D40BD010-EC6DR7040509030-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR7040509030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4518.8 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792688

CATALOG NUMBER: LER6D40BD010-EC6DR7040509030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P792688

CATALOG NUMBER: LER6D40BD010-EC6DR7040509030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	555099
5°	538607
10°	523589
15°	516721
20°	482509
25°	362487
30°	256251
35°	90767
40°	47724
45°	50836
50°	52643
55°	53623
60°	53953
65°	52818
70°	49867
75°	46183
80°	41024
85°	33221

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 53970 cd/sqm



TEST NUMBER: P792688

CATALOG NUMBER: LER6D40BD010-EC6DR7040509030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	463.2	10.3
10°-20°	1270.5	28.1
20°-30°	1399.3	31.0
30°-40°	534.6	11.8
40°-50°	252.4	5.6
50°-60°	250.9	5.6
60°-70°	200.9	4.4
70°-80°	115.5	2.6
80°-90°	31.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3133.0	69.3
0°-40°	3667.6	81.2
0°-60°	4171.0	92.3
0°-90°	4518.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4518.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5080	
5°	4911	463
15°	4568	1271
25°	3007	1399
35°	680	535
45°	329	252
55°	282	251
65°	204	201
75°	109	116
85°	26	31
90°	0	



TEST NUMBER: P792688

CATALOG NUMBER: LER6D40BD010-EC6DR7040509030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5080.5
2.5°	5027.4
5°	4910.8
7.5°	4813.4
10°	4719.3
12.5°	4639.7
15°	4568.1
17.5°	4395.1
20°	4149.8
22.5°	3620.5
25°	3006.8
27.5°	2617.5
30°	2031.1
32.5°	1311.9
35°	680.5
37.5°	367.6
40°	334.6
42.5°	332.2
45°	329.0
47.5°	321.8
50°	309.7
52.5°	296.0
55°	281.5
57.5°	265.4
60°	246.9
62.5°	226.0
65°	204.3
67.5°	180.2
70°	156.1
72.5°	131.9
75°	109.4
77.5°	86.1
80°	65.2
82.5°	45.8
85°	26.5
87.5°	10.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)