

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791676

Luminaire Tested: LER6D30D010-EC6DR6520359027-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791676
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR6520359027-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4968.9 lumens
Efficiency: N/A
Efficacy: 171.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791676

CATALOG NUMBER: LER6D30D010-EC6DR6520359027-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P791676

CATALOG NUMBER: LER6D30D010-EC6DR6520359027-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	263495
5°	262831
10°	262608
15°	254512
20°	231703
25°	201915
30°	167937
35°	133063
40°	96041
45°	60675
50°	31628
55°	16811
60°	8831
65°	4851
70°	2032
75°	2234
80°	1547
85°	1340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 60675 cd/sqm



TEST NUMBER: P791676

CATALOG NUMBER: LER6D30D010-EC6DR6520359027-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.7	8.6
10°-20°	1168.3	23.5
20°-30°	1428.1	28.7
30°-40°	1158.7	23.3
40°-50°	577.4	11.6
50°-60°	161.1	3.2
60°-70°	36.6	0.7
70°-80°	9.5	0.2
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3023.1	60.8
0°-40°	4181.9	84.2
0°-60°	4920.4	99.0
0°-90°	4968.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4968.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4512	
5°	4483	427
15°	4209	1168
25°	3133	1428
35°	1866	1159
45°	735	577
55°	165	161
65°	35	37
75°	10	10
85°	2	2
90°	0	



TEST NUMBER: P791676

CATALOG NUMBER: LER6D30D010-EC6DR6520359027-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4511.6
2.5°	4508.3
5°	4483.1
7.5°	4468.5
10°	4428.1
12.5°	4345.9
15°	4209.3
17.5°	3995.8
20°	3728.0
22.5°	3438.9
25°	3133.3
27.5°	2806.4
30°	2490.2
32.5°	2177.9
35°	1866.3
37.5°	1555.4
40°	1259.7
42.5°	982.5
45°	734.6
47.5°	511.8
50°	348.1
52.5°	240.0
55°	165.1
57.5°	111.4
60°	75.6
62.5°	52.4
65°	35.1
67.5°	17.9
70°	11.9
72.5°	11.3
75°	9.9
77.5°	6.6
80°	4.6
82.5°	3.3
85°	2.0
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)