

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791678

Luminaire Tested: LER6D30D010-EC6DR6520359027-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791678  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D30D010-EC6DR6520359027-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4721.5 lumens  
Efficiency: N/A  
Efficacy: 162.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P791678

CATALOG NUMBER: LER6D30D010-EC6DR6520359027-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P791678

CATALOG NUMBER: LER6D30D010-EC6DR6520359027-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	250377
5°	249745
10°	249537
15°	241844
20°	220168
25°	191862
30°	159574
35°	126440
40°	91260
45°	57652
50°	30047
55°	15976
60°	8387
65°	4616
70°	1930
75°	2121
80°	1480
85°	1273

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 57652 cd/sqm



TEST NUMBER: P791678

CATALOG NUMBER: LER6D30D010-EC6DR6520359027-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	405.4	8.6
10°-20°	1110.2	23.5
20°-30°	1357.0	28.7
30°-40°	1101.0	23.3
40°-50°	548.7	11.6
50°-60°	153.0	3.2
60°-70°	34.8	0.7
70°-80°	9.0	0.2
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2872.6	60.8
0°-40°	3973.7	84.2
0°-60°	4675.4	99.0
0°-90°	4721.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4721.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4287	
5°	4260	405
15°	4000	1110
25°	2977	1357
35°	1773	1101
45°	698	549
55°	157	153
65°	33	35
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P791678

CATALOG NUMBER: LER6D30D010-EC6DR6520359027-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4287.0
2.5°	4283.9
5°	4259.9
7.5°	4246.1
10°	4207.7
12.5°	4129.5
15°	3999.8
17.5°	3796.9
20°	3542.4
22.5°	3267.7
25°	2977.3
27.5°	2666.7
30°	2366.2
32.5°	2069.5
35°	1773.4
37.5°	1477.9
40°	1197.0
42.5°	933.6
45°	698.0
47.5°	486.3
50°	330.7
52.5°	228.1
55°	156.9
57.5°	105.8
60°	71.8
62.5°	49.8
65°	33.4
67.5°	17.0
70°	11.3
72.5°	10.7
75°	9.4
77.5°	6.3
80°	4.4
82.5°	3.1
85°	1.9
87.5°	1.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)