

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791680

Luminaire Tested: LER6D30D010-EC6DR6520359030-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791680
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR6520359030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4874.1 lumens
Efficiency: N/A
Efficacy: 168.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791680
CATALOG NUMBER: LER6D30D010-EC6DR6520359030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P791680

CATALOG NUMBER: LER6D30D010-EC6DR6520359030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	524331
5°	524766
10°	543237
15°	544140
20°	500973
25°	426852
30°	326776
35°	230859
40°	136268
45°	55317
50°	20058
55°	11163
60°	6403
65°	3516
70°	3706
75°	2871
80°	3020
85°	2507

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55317 cd/sqm



TEST NUMBER: P791680

CATALOG NUMBER: LER6D30D010-EC6DR6520359030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	462.1	9.5
10°-20°	1332.9	27.3
20°-30°	1599.3	32.8
30°-40°	1074.8	22.1
40°-50°	321.7	6.6
50°-60°	56.8	1.2
60°-70°	16.1	0.3
70°-80°	7.9	0.2
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3394.3	69.6
0°-40°	4469.1	91.7
0°-60°	4847.6	99.5
0°-90°	4874.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4874.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4799	
5°	4785	462
15°	4810	1333
25°	3541	1599
35°	1731	1075
45°	358	322
55°	59	57
65°	14	16
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P791680

CATALOG NUMBER: LER6D30D010-EC6DR6520359030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4798.9
2.5°	4819.4
5°	4784.6
7.5°	4856.9
10°	4896.4
12.5°	4886.9
15°	4810.5
17.5°	4623.6
20°	4308.6
22.5°	3937.6
25°	3540.7
27.5°	3092.7
30°	2590.1
32.5°	2134.5
35°	1730.8
37.5°	1331.9
40°	955.4
42.5°	624.0
45°	358.0
47.5°	189.6
50°	118.0
52.5°	81.8
55°	58.6
57.5°	42.3
60°	29.3
62.5°	19.1
65°	13.6
67.5°	12.3
70°	11.6
72.5°	8.9
75°	6.8
77.5°	6.1
80°	4.8
82.5°	3.4
85°	2.0
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)