

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791688

Luminaire Tested: LER6D30D010-EC6DR6520359035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR6520359035-6LB DP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5145.5 lumens
Efficiency: N/A
Efficacy: 177.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791688
CATALOG NUMBER: LER6D30D010-EC6DR6520359035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P791688

CATALOG NUMBER: LER6D30D010-EC6DR6520359035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	553526
5°	553984
10°	573481
15°	574432
20°	528867
25°	450614
30°	344969
35°	243717
40°	143856
45°	58408
50°	21162
55°	11791
60°	6774
65°	3723
70°	3897
75°	3039
80°	3146
85°	2758

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 58408 cd/sqm



TEST NUMBER: P791688

CATALOG NUMBER: LER6D30D010-EC6DR6520359035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	487.8	9.5
10°-20°	1407.1	27.3
20°-30°	1688.3	32.8
30°-40°	1134.6	22.1
40°-50°	339.6	6.6
50°-60°	59.9	1.2
60°-70°	17.1	0.3
70°-80°	8.4	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3583.3	69.6
0°-40°	4717.9	91.7
0°-60°	5117.4	99.5
0°-90°	5145.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5145.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5066	
5°	5051	488
15°	5078	1407
25°	3738	1688
35°	1827	1135
45°	378	340
55°	62	60
65°	14	17
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P791688

CATALOG NUMBER: LER6D30D010-EC6DR6520359035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5066.1
2.5°	5087.7
5°	5051.0
7.5°	5127.3
10°	5169.0
12.5°	5159.0
15°	5078.3
17.5°	4881.1
20°	4548.5
22.5°	4156.8
25°	3737.8
27.5°	3264.8
30°	2734.3
32.5°	2253.4
35°	1827.2
37.5°	1406.0
40°	1008.6
42.5°	658.7
45°	378.0
47.5°	200.1
50°	124.5
52.5°	86.4
55°	61.9
57.5°	44.6
60°	31.0
62.5°	20.2
65°	14.4
67.5°	13.0
70°	12.2
72.5°	9.4
75°	7.2
77.5°	6.5
80°	5.0
82.5°	3.6
85°	2.2
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)