

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791692

Luminaire Tested: LER6D30D010-EC6DR6520359035-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791692  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D30D010-EC6DR6520359035-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5416.3 lumens  
Efficiency: N/A  
Efficacy: 186.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P791692  
CATALOG NUMBER: LER6D30D010-EC6DR6520359035-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P791692

CATALOG NUMBER: LER6D30D010-EC6DR6520359035-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	287219
5°	286498
10°	286253
15°	277428
20°	252561
25°	220094
30°	183056
35°	145041
40°	104686
45°	66134
50°	34472
55°	18318
60°	9625
65°	5293
70°	2220
75°	2437
80°	1715
85°	1474

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 66134 cd/sqm



TEST NUMBER: P791692

CATALOG NUMBER: LER6D30D010-EC6DR6520359035-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	465.1	8.6
10°-20°	1273.5	23.5
20°-30°	1556.7	28.7
30°-40°	1263.1	23.3
40°-50°	629.4	11.6
50°-60°	175.5	3.2
60°-70°	39.9	0.7
70°-80°	10.4	0.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3295.3	60.8
0°-40°	4558.4	84.2
0°-60°	5363.3	99.0
0°-90°	5416.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5416.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4918	
5°	4887	465
15°	4588	1274
25°	3415	1557
35°	2034	1263
45°	801	629
55°	180	176
65°	38	40
75°	11	10
85°	2	3
90°	0	



TEST NUMBER: P791692

CATALOG NUMBER: LER6D30D010-EC6DR6520359035-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4917.8
2.5°	4914.2
5°	4886.8
7.5°	4870.9
10°	4826.8
12.5°	4737.2
15°	4588.3
17.5°	4355.6
20°	4063.6
22.5°	3748.6
25°	3415.4
27.5°	3059.1
30°	2714.4
32.5°	2374.0
35°	2034.3
37.5°	1695.4
40°	1373.1
42.5°	1071.0
45°	800.7
47.5°	557.9
50°	379.4
52.5°	261.6
55°	179.9
57.5°	121.4
60°	82.4
62.5°	57.1
65°	38.3
67.5°	19.5
70°	13.0
72.5°	12.3
75°	10.8
77.5°	7.2
80°	5.1
82.5°	3.6
85°	2.2
87.5°	1.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)