

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792768

Luminaire Tested: LER6D45BD010-EC6DR3040509024-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P792768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR3040509024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4103.3 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792768

CATALOG NUMBER: LER6D45BD010-EC6DR3040509024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P792768

CATALOG NUMBER: LER6D45BD010-EC6DR3040509024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1009929	1009929	1009929
5°	980939	979794	980985
10°	849642	843650	849440
15°	554348	551369	548603
20°	275655	285991	275280
25°	138855	156582	136008
30°	55594	60579	48435
35°	25790	24697	20697
40°	11131	12360	10482
45°	7859	9742	7924
50°	2703	7097	2858
55°	1561	2936	1641
60°	1087	1286	1087
65°	706	706	706
70°	425	291	425
75°	0	177	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 9742 cd/sqm



TEST NUMBER: P792768

CATALOG NUMBER: LER6D45BD010-EC6DR3040509024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1160.2	28.3
10°-20°	1868.6	45.5
20°-30°	807.5	19.7
30°-40°	184.0	4.5
40°-50°	63.2	1.5
50°-60°	15.4	0.4
60°-70°	4.0	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3836.3	93.5
0°-40°	4020.3	98.0
0°-60°	4098.9	99.9
0°-90°	4103.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4103.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	13194	13194	13194	13194	13194	
5°	12767	12754	12752	12778	12767	1161
15°	6996	6911	6958	6935	6923	1873
25°	1644	1706	1854	1663	1610	787
35°	276	282	264	262	222	187
45°	73	90	90	90	73	52
55°	12	12	22	13	12	11
65°	4	4	4	4	4	4
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P792768

CATALOG NUMBER: LER6D45BD010-EC6DR3040509024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	13194.2	13194.2	13194.2	13194.2	13194.2
2.5°	13106.8	13097.7	13102.9	13109.4	13112.0
5°	12766.7	12754.4	12751.8	12778.4	12767.3
7.5°	12080.7	12063.2	12036.6	12096.9	12153.2
10°	10931.5	10912.1	10854.4	10882.9	10928.9
12.5°	9234.9	9172.1	9170.8	9261.5	9249.2
15°	6995.5	6911.3	6957.9	6935.3	6923.0
17.5°	4704.3	4671.9	4734.1	4715.3	4634.3
20°	3384.1	3392.5	3511.0	3451.4	3379.5
22.5°	2469.4	2499.8	2640.4	2486.9	2430.5
25°	1644.1	1706.3	1854.0	1662.9	1610.4
27.5°	1011.2	1039.7	1189.3	998.2	969.7
30°	629.0	614.8	685.4	588.2	548.0
32.5°	412.6	394.5	417.2	374.4	342.0
35°	276.0	281.8	264.3	262.4	221.5
37.5°	172.3	198.2	174.9	186.6	142.5
40°	111.4	143.8	123.7	136.7	104.9
42.5°	91.3	110.8	101.7	108.2	93.3
45°	72.6	90.0	90.0	90.0	73.2
47.5°	40.2	60.2	77.1	61.5	42.8
50°	22.7	30.4	59.6	31.7	24.0
52.5°	15.5	17.5	40.8	18.1	16.2
55°	11.7	12.3	22.0	13.0	12.3
57.5°	9.1	9.7	11.7	9.7	9.1
60°	7.1	7.1	8.4	7.8	7.1
62.5°	5.2	5.2	5.8	5.2	5.2
65°	3.9	3.9	3.9	3.9	3.9
67.5°	1.9	2.6	2.6	2.6	2.6
70°	1.9	1.3	1.3	1.3	1.9
72.5°	1.3	0.6	0.6	0.6	0.6
75°	0.0	0.0	0.6	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)