

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791708

Luminaire Tested: LER6D30D010-EC6DR6520359050-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR6520359050-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5500.4 lumens
Efficiency: N/A
Efficacy: 189.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791708
CATALOG NUMBER: LER6D30D010-EC6DR6520359050-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P791708
 CATALOG NUMBER: LER6D30D010-EC6DR6520359050-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	291681
5°	290948
10°	290700
15°	281739
20°	256489
25°	223509
30°	185902
35°	147294
40°	106310
45°	67167
50°	35008
55°	18603
60°	9777
65°	5376
70°	2254
75°	2482
80°	1715
85°	1474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 67167 cd/sqm



TEST NUMBER: P791708

CATALOG NUMBER: LER6D30D010-EC6DR6520359050-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.3	8.6
10°-20°	1293.3	23.5
20°-30°	1580.9	28.7
30°-40°	1282.7	23.3
40°-50°	639.2	11.6
50°-60°	178.3	3.2
60°-70°	40.5	0.7
70°-80°	10.5	0.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3346.5	60.8
0°-40°	4629.2	84.2
0°-60°	5446.7	99.0
0°-90°	5500.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5500.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4994	
5°	4963	472
15°	4660	1293
25°	3468	1581
35°	2066	1283
45°	813	639
55°	183	178
65°	39	41
75°	11	11
85°	2	3
90°	0	



TEST NUMBER: P791708

CATALOG NUMBER: LER6D30D010-EC6DR6520359050-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4994.2
2.5°	4990.6
5°	4962.7
7.5°	4946.5
10°	4901.8
12.5°	4810.8
15°	4659.6
17.5°	4423.3
20°	4126.8
22.5°	3806.8
25°	3468.4
27.5°	3106.6
30°	2756.6
32.5°	2410.9
35°	2065.9
37.5°	1721.7
40°	1394.4
42.5°	1087.6
45°	813.2
47.5°	566.6
50°	385.3
52.5°	265.7
55°	182.7
57.5°	123.3
60°	83.7
62.5°	58.0
65°	38.9
67.5°	19.8
70°	13.2
72.5°	12.5
75°	11.0
77.5°	7.3
80°	5.1
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)