

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791727

Luminaire Tested: LER6D30D010-EC6DR7020359030-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR7020359030-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3266.8 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791727
CATALOG NUMBER: LER6D30D010-EC6DR7020359030-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P791727

CATALOG NUMBER: LER6D30D010-EC6DR7020359030-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	401304
5°	389379
10°	378527
15°	373551
20°	348819
25°	262052
30°	185246
35°	65624
40°	34502
45°	36744
50°	38058
55°	38765
60°	39006
65°	38185
70°	36035
75°	33392
80°	29636
85°	24070

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 39023 cd/sqm



TEST NUMBER: P791727

CATALOG NUMBER: LER6D30D010-EC6DR7020359030-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.9	10.3
10°-20°	918.5	28.1
20°-30°	1011.6	31.0
30°-40°	386.5	11.8
40°-50°	182.5	5.6
50°-60°	181.4	5.6
60°-70°	145.3	4.4
70°-80°	83.5	2.6
80°-90°	22.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2264.9	69.3
0°-40°	2651.5	81.2
0°-60°	3015.4	92.3
0°-90°	3266.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3266.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3673	
5°	3550	335
15°	3302	918
25°	2174	1012
35°	492	387
45°	238	182
55°	204	181
65°	148	145
75°	79	83
85°	19	23
90°	0	



TEST NUMBER: P791727

CATALOG NUMBER: LER6D30D010-EC6DR7020359030-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3672.9
2.5°	3634.5
5°	3550.2
7.5°	3479.8
10°	3411.8
12.5°	3354.2
15°	3302.4
17.5°	3177.4
20°	3000.0
22.5°	2617.4
25°	2173.7
27.5°	1892.3
30°	1468.3
32.5°	948.5
35°	492.0
37.5°	265.8
40°	241.9
42.5°	240.2
45°	237.8
47.5°	232.6
50°	223.9
52.5°	214.0
55°	203.5
57.5°	191.9
60°	178.5
62.5°	163.4
65°	147.7
67.5°	130.3
70°	112.8
72.5°	95.4
75°	79.1
77.5°	62.2
80°	47.1
82.5°	33.1
85°	19.2
87.5°	7.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)