

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791730

Luminaire Tested: LER6D30D010-EC6DR7020359030-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR7020359030-6LBDDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4385.7 lumens
Efficiency: N/A
Efficacy: 151.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791730
CATALOG NUMBER: LER6D30D010-EC6DR7020359030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P791730

CATALOG NUMBER: LER6D30D010-EC6DR7020359030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	538743
5°	522737
10°	508167
15°	501496
20°	468289
25°	351806
30°	248693
35°	88099
40°	46326
45°	49338
50°	51096
55°	52042
60°	52380
65°	51267
70°	48398
75°	44832
80°	39766
85°	32344

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 52383 cd/sqm



TEST NUMBER: P791730

CATALOG NUMBER: LER6D30D010-EC6DR7020359030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	449.5	10.3
10°-20°	1233.1	28.1
20°-30°	1358.1	31.0
30°-40°	518.9	11.8
40°-50°	245.0	5.6
50°-60°	243.6	5.6
60°-70°	195.0	4.4
70°-80°	112.1	2.6
80°-90°	30.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3040.7	69.3
0°-40°	3559.6	81.2
0°-60°	4048.2	92.3
0°-90°	4385.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4385.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4931	
5°	4766	450
15°	4434	1233
25°	2918	1358
35°	660	519
45°	319	245
55°	273	244
65°	198	195
75°	106	112
85°	26	30
90°	0	



TEST NUMBER: P791730

CATALOG NUMBER: LER6D30D010-EC6DR7020359030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4930.8
2.5°	4879.3
5°	4766.1
7.5°	4671.6
10°	4580.3
12.5°	4503.0
15°	4433.5
17.5°	4265.7
20°	4027.5
22.5°	3513.9
25°	2918.2
27.5°	2540.3
30°	1971.2
32.5°	1273.3
35°	660.5
37.5°	356.8
40°	324.8
42.5°	322.4
45°	319.3
47.5°	312.3
50°	300.6
52.5°	287.3
55°	273.2
57.5°	257.6
60°	239.7
62.5°	219.4
65°	198.3
67.5°	174.9
70°	151.5
72.5°	128.0
75°	106.2
77.5°	83.5
80°	63.2
82.5°	44.5
85°	25.8
87.5°	10.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)