

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793057

Luminaire Tested: LER6D45BD010-EC6DR6040509024-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P793057  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D45BD010-EC6DR6040509024-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4424.6 lumens  
Efficiency: N/A  
Efficacy: 114.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P793057

CATALOG NUMBER: LER6D45BD010-EC6DR6040509024-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P793057

CATALOG NUMBER: LER6D45BD010-EC6DR6040509024-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	574132
5°	588259
10°	595360
15°	567159
20°	500066
25°	404465
30°	273585
35°	137091
40°	22236
45°	21772
50°	22199
55°	22535
60°	23163
65°	23682
70°	24247
75°	24527
80°	23658
85°	19682

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 24527 cd/sqm



TEST NUMBER: P793057

CATALOG NUMBER: LER6D45BD010-EC6DR6040509024-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	512.6	11.6
10°-20°	1386.9	31.3
20°-30°	1492.2	33.7
30°-40°	648.6	14.7
40°-50°	108.9	2.5
50°-60°	105.9	2.4
60°-70°	90.6	2.0
70°-80°	60.6	1.4
80°-90°	18.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3391.7	76.7
0°-40°	4040.3	91.3
0°-60°	4255.2	96.2
0°-90°	4424.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4424.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5255	
5°	5364	513
15°	5014	1387
25°	3355	1492
35°	1028	649
45°	141	109
55°	118	106
65°	92	91
75°	58	61
85°	16	18
90°	0	



TEST NUMBER: P793057

CATALOG NUMBER: LER6D45BD010-EC6DR6040509024-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5254.7
2.5°	5402.4
5°	5363.5
7.5°	5375.8
10°	5366.2
12.5°	5255.4
15°	5014.0
17.5°	4689.9
20°	4300.8
22.5°	3884.3
25°	3355.0
27.5°	2683.4
30°	2168.5
32.5°	1671.3
35°	1027.8
37.5°	439.7
40°	155.9
42.5°	143.6
45°	140.9
47.5°	136.1
50°	130.6
52.5°	124.5
55°	118.3
57.5°	112.2
60°	106.0
62.5°	99.2
65°	91.6
67.5°	84.1
70°	75.9
72.5°	67.0
75°	58.1
77.5°	47.9
80°	37.6
82.5°	26.7
85°	15.7
87.5°	5.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)