

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793087

Luminaire Tested: LER6D45BD010-EC6DR6040509040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR6040509040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4096.2 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793087

CATALOG NUMBER: LER6D45BD010-EC6DR6040509040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P793087

CATALOG NUMBER: LER6D45BD010-EC6DR6040509040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	531532
5°	544607
10°	551181
15°	525080
20°	462952
25°	374447
30°	253286
35°	126927
40°	20581
45°	20149
50°	20551
55°	20859
60°	21437
65°	21924
70°	22458
75°	22712
80°	21896
85°	18303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 22712 cd/sqm



TEST NUMBER: P793087

CATALOG NUMBER: LER6D45BD010-EC6DR6040509040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	474.6	11.6
10°-20°	1284.0	31.3
20°-30°	1381.5	33.7
30°-40°	600.5	14.7
40°-50°	100.9	2.5
50°-60°	98.0	2.4
60°-70°	83.9	2.0
70°-80°	56.1	1.4
80°-90°	16.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3140.0	76.7
0°-40°	3740.5	91.3
0°-60°	3939.4	96.2
0°-90°	4096.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4096.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4865	
5°	4966	475
15°	4642	1284
25°	3106	1381
35°	952	600
45°	130	101
55°	110	98
65°	85	84
75°	54	56
85°	15	17
90°	0	



TEST NUMBER: P793087

CATALOG NUMBER: LER6D45BD010-EC6DR6040509040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4864.8
2.5°	5001.6
5°	4965.5
7.5°	4976.9
10°	4968.0
12.5°	4865.5
15°	4642.0
17.5°	4341.9
20°	3981.6
22.5°	3596.1
25°	3106.0
27.5°	2484.3
30°	2007.6
32.5°	1547.3
35°	951.6
37.5°	407.1
40°	144.3
42.5°	133.0
45°	130.4
47.5°	126.0
50°	120.9
52.5°	115.2
55°	109.5
57.5°	103.8
60°	98.1
62.5°	91.8
65°	84.8
67.5°	77.9
70°	70.3
72.5°	62.0
75°	53.8
77.5°	44.3
80°	34.8
82.5°	24.7
85°	14.6
87.5°	5.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)