

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791950

Luminaire Tested: LER6D35BD010-EC6DR4020359050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR4020359050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4229.2 lumens
Efficiency: N/A
Efficacy: 137.3 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791950
CATALOG NUMBER: LER6D35BD010-EC6DR4020359050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P791950

CATALOG NUMBER: LER6D35BD010-EC6DR4020359050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96											96																	
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92											92																	
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88											88																	
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84											84																	
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81											81																	
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77											77																	
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74											74																	
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72											72																	
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69											69																	
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67											67																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1075847
5°	1070623
10°	1011974
15°	860308
20°	586364
25°	244656
30°	76922
35°	35760
40°	19768
45°	9070
50°	4402
55°	2419
60°	1267
65°	440
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9070 cd/sqm



TEST NUMBER: P791950

CATALOG NUMBER: LER6D35BD010-EC6DR4020359050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	911.5	21.6
10°-20°	2042.0	48.3
20°-30°	1022.1	24.2
30°-40°	187.4	4.4
40°-50°	51.7	1.2
50°-60°	12.2	0.3
60°-70°	2.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3975.6	94.0
0°-40°	4162.9	98.4
0°-60°	4226.8	99.9
0°-90°	4229.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4229.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9847	
5°	9762	911
15°	7606	2042
25°	2029	1022
35°	268	187
45°	59	52
55°	13	12
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791950
CATALOG NUMBER: LER6D35BD010-EC6DR4020359050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	9846.6
2.5°	9832.2
5°	9761.5
7.5°	9536.0
10°	9121.3
12.5°	8474.7
15°	7605.6
17.5°	6475.3
20°	5043.0
22.5°	3438.1
25°	2029.4
27.5°	1072.8
30°	609.7
32.5°	394.0
35°	268.1
37.5°	191.5
40°	138.6
42.5°	94.9
45°	58.7
47.5°	37.4
50°	25.9
52.5°	18.4
55°	12.7
57.5°	8.1
60°	5.8
62.5°	3.5
65°	1.7
67.5°	1.2
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)