

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792042

Luminaire Tested: LER6D35BD010-EC6DR5020359050-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P792042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR5020359050-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3997.2 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792042

CATALOG NUMBER: LER6D35BD010-EC6DR5020359050-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P792042

CATALOG NUMBER: LER6D35BD010-EC6DR5020359050-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95			95																
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			90																
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85			85																
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80			80																
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76			76																
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72			72																
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69			69																
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65			65																
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62			62																
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59			59																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	703683
5°	696313
10°	684838
15°	623603
20°	518903
25°	368347
30°	194973
35°	79456
40°	29510
45°	13505
50°	5541
55°	2895
60°	1420
65°	414
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13505 cd/sqm



TEST NUMBER: P792042

CATALOG NUMBER: LER6D35BD010-EC6DR5020359050-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	600.1	15.0
10°-20°	1516.5	37.9
20°-30°	1362.2	34.1
30°-40°	426.5	10.7
40°-50°	74.7	1.9
50°-60°	14.9	0.4
60°-70°	2.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3478.8	87.0
0°-40°	3905.4	97.7
0°-60°	3994.9	99.9
0°-90°	3997.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3997.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6440	
5°	6349	600
15°	5513	1517
25°	3055	1362
35°	596	427
45°	87	75
55°	15	15
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P792042

CATALOG NUMBER: LER6D35BD010-EC6DR5020359050-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6440.4
2.5°	6408.4
5°	6348.7
7.5°	6257.4
10°	6172.7
12.5°	5901.2
15°	5513.0
17.5°	5020.0
20°	4462.8
22.5°	3818.3
25°	3055.4
27.5°	2246.4
30°	1545.4
32.5°	1006.2
35°	595.7
37.5°	342.1
40°	206.9
42.5°	134.7
45°	87.4
47.5°	53.2
50°	32.6
52.5°	22.3
55°	15.2
57.5°	10.3
60°	6.5
62.5°	3.8
65°	1.6
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)