

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793107

Luminaire Tested: LER6D45BD010-EC6DR6540509024-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P793107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR6540509024-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3598.5 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P793107
CATALOG NUMBER: LER6D45BD010-EC6DR6540509024-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P793107

CATALOG NUMBER: LER6D45BD010-EC6DR6540509024-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	190823
5°	190344
10°	190179
15°	184319
20°	167798
25°	146224
30°	121619
35°	96366
40°	69555
45°	43941
50°	22906
55°	12178
60°	6389
65°	3510
70°	1469
75°	1625
80°	1144
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43941 cd/sqm



TEST NUMBER: P793107

CATALOG NUMBER: LER6D45BD010-EC6DR6540509024-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.0	8.6
10°-20°	846.1	23.5
20°-30°	1034.2	28.7
30°-40°	839.2	23.3
40°-50°	418.2	11.6
50°-60°	116.7	3.2
60°-70°	26.5	0.7
70°-80°	6.9	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2189.4	60.8
0°-40°	3028.5	84.2
0°-60°	3563.4	99.0
0°-90°	3598.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3598.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3267	
5°	3247	309
15°	3048	846
25°	2269	1034
35°	1352	839
45°	532	418
55°	120	117
65°	25	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P793107

CATALOG NUMBER: LER6D45BD010-EC6DR6540509024-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3267.3
2.5°	3264.9
5°	3246.7
7.5°	3236.1
10°	3206.8
12.5°	3147.3
15°	3048.4
17.5°	2893.8
20°	2699.8
22.5°	2490.5
25°	2269.1
27.5°	2032.4
30°	1803.4
32.5°	1577.2
35°	1351.6
37.5°	1126.4
40°	912.3
42.5°	711.6
45°	532.0
47.5°	370.7
50°	252.1
52.5°	173.8
55°	119.6
57.5°	80.7
60°	54.7
62.5°	37.9
65°	25.4
67.5°	13.0
70°	8.6
72.5°	8.2
75°	7.2
77.5°	4.8
80°	3.4
82.5°	2.4
85°	1.4
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)