

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792105

Luminaire Tested: LER6D35BD010-EC6DR6020359027-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792105  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D35BD010-EC6DR6020359027-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3886.8 lumens  
Efficiency: N/A  
Efficacy: 126.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P792105

CATALOG NUMBER: LER6D35BD010-EC6DR6020359027-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P792105

CATALOG NUMBER: LER6D35BD010-EC6DR6020359027-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	504359
5°	516759
10°	523001
15°	498227
20°	439291
25°	355302
30°	240329
35°	120431
40°	19540
45°	19129
50°	19497
55°	19792
60°	20344
65°	20812
70°	21308
75°	21572
80°	20764
85°	17300

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 21572 cd/sqm



TEST NUMBER: P792105

CATALOG NUMBER: LER6D35BD010-EC6DR6020359027-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	450.3	11.6
10°-20°	1218.3	31.3
20°-30°	1310.8	33.7
30°-40°	569.8	14.7
40°-50°	95.7	2.5
50°-60°	93.0	2.4
60°-70°	79.6	2.0
70°-80°	53.3	1.4
80°-90°	15.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2979.5	76.7
0°-40°	3549.3	91.3
0°-60°	3738.0	96.2
0°-90°	3886.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3886.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4616	
5°	4712	450
15°	4405	1218
25°	2947	1311
35°	903	570
45°	124	96
55°	104	93
65°	80	80
75°	51	53
85°	14	16
90°	0	



TEST NUMBER: P792105

CATALOG NUMBER: LER6D35BD010-EC6DR6020359027-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4616.1
2.5°	4745.8
5°	4711.6
7.5°	4722.4
10°	4714.0
12.5°	4616.7
15°	4404.6
17.5°	4119.9
20°	3778.1
22.5°	3412.2
25°	2947.2
27.5°	2357.3
30°	1904.9
32.5°	1468.2
35°	902.9
37.5°	386.3
40°	137.0
42.5°	126.2
45°	123.8
47.5°	119.5
50°	114.7
52.5°	109.3
55°	103.9
57.5°	98.5
60°	93.1
62.5°	87.1
65°	80.5
67.5°	73.9
70°	66.7
72.5°	58.9
75°	51.1
77.5°	42.1
80°	33.0
82.5°	23.4
85°	13.8
87.5°	4.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)