

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792116

Luminaire Tested: LER6D35BD010-EC6DR6020359030-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792116  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D35BD010-EC6DR6020359030-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4014.3 lumens  
Efficiency: N/A  
Efficacy: 130.3 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P792116  
CATALOG NUMBER: LER6D35BD010-EC6DR6020359030-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P792116

CATALOG NUMBER: LER6D35BD010-EC6DR6020359030-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65		
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57		
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53		
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	438933
5°	437857
10°	452406
15°	452867
20°	416687
25°	354422
30°	270053
35°	190977
40°	112136
45°	45243
50°	15111
55°	7277
60°	2994
65°	440
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 45243 cd/sqm



TEST NUMBER: P792116

CATALOG NUMBER: LER6D35BD010-EC6DR6020359030-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	385.1	9.6
10°-20°	1109.1	27.6
20°-30°	1327.5	33.1
30°-40°	887.9	22.1
40°-50°	263.2	6.6
50°-60°	37.9	0.9
60°-70°	3.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2821.7	70.3
0°-40°	3709.6	92.4
0°-60°	4010.7	99.9
0°-90°	4014.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4014.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4017	
5°	3992	385
15°	4004	1109
25°	2940	1327
35°	1432	888
45°	293	263
55°	38	38
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P792116

CATALOG NUMBER: LER6D35BD010-EC6DR6020359030-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4017.3
2.5°	4012.1
5°	3992.2
7.5°	4046.3
10°	4077.7
12.5°	4072.0
15°	4003.6
17.5°	3842.4
20°	3583.7
22.5°	3273.2
25°	2939.9
27.5°	2564.4
30°	2140.5
32.5°	1762.2
35°	1431.8
37.5°	1100.7
40°	786.2
42.5°	518.5
45°	292.8
47.5°	149.8
50°	88.9
52.5°	57.5
55°	38.2
57.5°	24.5
60°	13.7
62.5°	5.7
65°	1.7
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)