

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793162

Luminaire Tested: LER6D45BD010-EC6DR7040509027-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793162
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR7040509027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3752.9 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P793162
CATALOG NUMBER: LER6D45BD010-EC6DR7040509027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P793162

CATALOG NUMBER: LER6D45BD010-EC6DR7040509027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	461015
5°	447311
10°	434843
15°	429136
20°	400723
25°	301040
30°	212813
35°	75388
40°	39637
45°	42214
50°	43719
55°	44537
60°	44819
65°	43873
70°	41402
75°	38374
80°	34040
85°	27580

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 44839 cd/sqm



TEST NUMBER: P793162

CATALOG NUMBER: LER6D45BD010-EC6DR7040509027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	384.7	10.3
10°-20°	1055.2	28.1
20°-30°	1162.1	31.0
30°-40°	444.0	11.8
40°-50°	209.6	5.6
50°-60°	208.4	5.6
60°-70°	166.9	4.4
70°-80°	95.9	2.6
80°-90°	26.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2602.0	69.3
0°-40°	3046.0	81.2
0°-60°	3464.1	92.3
0°-90°	3752.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3752.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4219	
5°	4078	385
15°	3794	1055
25°	2497	1162
35°	565	444
45°	273	210
55°	234	208
65°	170	167
75°	91	96
85°	22	26
90°	0	



TEST NUMBER: P793162

CATALOG NUMBER: LER6D45BD010-EC6DR7040509027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4219.4
2.5°	4175.3
5°	4078.4
7.5°	3997.6
10°	3919.4
12.5°	3853.3
15°	3793.8
17.5°	3650.2
20°	3446.4
22.5°	3006.9
25°	2497.1
27.5°	2173.8
30°	1686.8
32.5°	1089.6
35°	565.2
37.5°	305.3
40°	277.9
42.5°	275.9
45°	273.2
47.5°	267.2
50°	257.2
52.5°	245.8
55°	233.8
57.5°	220.5
60°	205.1
62.5°	187.7
65°	169.7
67.5°	149.6
70°	129.6
72.5°	109.6
75°	90.9
77.5°	71.5
80°	54.1
82.5°	38.1
85°	22.0
87.5°	8.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)