

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792175

Luminaire Tested: LER6D35BD010-EC6DR6520359040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792175
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR6520359040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2625.5 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792175

CATALOG NUMBER: LER6D35BD010-EC6DR6520359040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P792175

CATALOG NUMBER: LER6D35BD010-EC6DR6520359040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	282439
5°	282673
10°	292632
15°	293115
20°	269858
25°	229936
30°	176023
35°	124353
40°	73412
45°	29807
50°	10811
55°	6019
60°	3453
65°	1887
70°	1981
75°	1562
80°	1636
85°	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29807 cd/sqm



TEST NUMBER: P792175

CATALOG NUMBER: LER6D35BD010-EC6DR6520359040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.9	9.5
10°-20°	718.0	27.3
20°-30°	861.5	32.8
30°-40°	578.9	22.0
40°-50°	173.3	6.6
50°-60°	30.6	1.2
60°-70°	8.7	0.3
70°-80°	4.3	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1828.4	69.6
0°-40°	2407.3	91.7
0°-60°	2611.3	99.5
0°-90°	2625.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2625.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2585	
5°	2577	249
15°	2591	718
25°	1907	861
35°	932	579
45°	193	173
55°	32	31
65°	7	9
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P792175

CATALOG NUMBER: LER6D35BD010-EC6DR6520359040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2585.0
2.5°	2596.1
5°	2577.3
7.5°	2616.3
10°	2637.6
12.5°	2632.4
15°	2591.3
17.5°	2490.6
20°	2320.9
22.5°	2121.1
25°	1907.3
27.5°	1665.9
30°	1395.2
32.5°	1149.8
35°	932.3
37.5°	717.4
40°	514.7
42.5°	336.1
45°	192.9
47.5°	102.1
50°	63.6
52.5°	44.1
55°	31.6
57.5°	22.8
60°	15.8
62.5°	10.3
65°	7.3
67.5°	6.6
70°	6.2
72.5°	4.8
75°	3.7
77.5°	3.3
80°	2.6
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)